

NEMA 3R, 12, and 13 Double-Door Wall-Mount



Applications

Designed to house electrical and electronic controls, instrumentation and components. Provides protection from dust, oil and water. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Gasketed overlapping doors eliminate need for a center post
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Concealed hinges
- Removable and interchangeable doors
- A removable print pocket is provided on door with 3-point latch.
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanel
- Ground studs on door and body
- Mounting hardware, sealing washers, and hole plugs are included.

Options

- Optional mounting feet are available ([SCE-ELMFK4](#)).

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



NEMA 3R, 12, and 13 Double-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 12, and 13 Double-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-244208WFLP	\$792.00	24.00 x 42.00 x 9.10 [610 x 1067 x 231]	PDF	SCE-42P24	\$142.00
SCE-244212WFLP	\$845.00	24.00 x 42.00 x 13.10 [610 x 1067 x 333]	PDF	SCE-42P24	\$142.00
SCE-244808WFLP	\$835.00	24.00 x 48.00 x 9.10 [610 x 1219 x 231]	PDF	SCE-48P24	\$154.00
SCE-244812WFLP	\$874.00	24.00 x 48.00 x 13.10 [610 x 1219 x 333]	PDF	SCE-48P24	\$154.00
SCE-304210WFLP	\$893.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	PDF	SCE-42P30	\$181.00
SCE-304810WFLP	\$946.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	PDF	SCE-48P30	\$201.00
SCE-306010WFLP	\$1,088.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	PDF	SCE-60P30	\$248.00
SCE-306012WFLP	\$1,172.00	30.00 x 60.00 x 13.10 [762 x 1524 x 333]	PDF	SCE-60P30	\$248.00
SCE-364212WFLP	\$1,007.00	36.00 x 42.00 x 13.10 [914 x 1067 x 333]	PDF	SCE-42P36	\$213.00
SCE-364216WFLP	\$1,096.00	36.00 x 42.00 x 17.10 [914 x 1067 x 434]	PDF	SCE-42P36	\$213.00
SCE-364810WFLP	\$1,082.00	36.00 x 48.00 x 11.10 [914 x 1219 x 282]	PDF	SCE-48P36	\$240.00
SCE-364812WFLP	\$1,099.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	PDF	SCE-48P36	\$240.00
SCE-364816WFLP	\$1,200.00	36.00 x 48.00 x 17.10 [914 x 1219 x 434]	PDF	SCE-48P36	\$240.00
SCE-366012WFLP	\$1,281.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	PDF	SCE-60P36	\$295.00
SCE-366016WFLP	\$1,427.00	36.00 x 60.00 x 17.10 [914 x 1524 x 434]	PDF	SCE-60P36	\$295.00
SCE-424212WFLP	\$1,112.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	PDF	SCE-42P42	\$244.00
SCE-424216WFLP	\$1,263.00	42.00 x 42.00 x 17.10 [1067 x 1067 x 434]	PDF	SCE-42P42	\$244.00
SCE-424812WFLP	\$1,214.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	PDF	SCE-48P42	\$276.00
SCE-424816WFLP	\$1,362.00	42.00 x 48.00 x 17.10 [1067 x 1219 x 434]	PDF	SCE-48P42	\$276.00
SCE-426012WFALP	\$1,416.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	PDF	SCE-60BFP42	\$358.00
SCE-426016WFALP	\$1,624.00	42.00 x 60.00 x 17.10 [1067 x 1524 x 434]	PDF	SCE-60BFP42	\$358.00
SCE-484812WFLP	\$1,325.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	PDF	SCE-48P48	\$331.00
SCE-484816WFLP	\$1,550.00	48.00 x 48.00 x 17.10 [1219 x 1219 x 434]	PDF	SCE-48P48	\$331.00

Note: Dimensions in inches [millimeters].