

NEMA 3R Screw Cover Wall-Mount



Applications

Designed to house electrical controls, instruments, and components in an outdoor environment. Protects against rain, sleet and snow.

Construction

- 16-gauge or 18-gauge galvanized steel
 - See drawings for details
- Spot weld construction
- Rain cap
- Mounting holes in back of enclosure
- Slip on removable screw cover
- Padlocking provisions
- No gasket
- No subpanel or provisions
- Ground studs on door and body

Note: Optional mounting straps available.

Finish

- ANSI 61 gray powder coated inside and out

Listings

- NEMA Type 3R
- cULus Listed Type 3R [File E69392]
- IEC 60529 IP32



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R Screw Cover Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link
SCE-4R44	\$65.00	4.00 x 4.16 x 4.35 [102 x 106 x 110]	PDF
SCE-6R64	\$69.00	6.00 x 6.16 x 4.35 [152 x 156 x 110]	PDF
SCE-6R66	\$72.00	6.00 x 6.16 x 6.35 [152 x 156 x 161]	PDF
SCE-8R64	\$78.00	8.00 x 6.16 x 4.35 [203 x 156 x 110]	PDF
SCE-8R66	\$86.00	8.00 x 6.16 x 6.35 [203 x 156 x 161]	PDF
SCE-10R84	\$96.00	10.00 x 8.16 x 4.35 [254 x 207 x 110]	PDF
SCE-10R86	\$102.00	10.00 x 8.16 x 6.35 [254 x 207 x 161]	PDF
SCE-10R104	\$116.00	10.00 x 10.16 x 4.35 [254 x 258 x 110]	PDF
SCE-10R106	\$136.00	10.00 x 10.16 x 6.35 [254 x 258 x 161]	PDF
SCE-12R104	\$145.00	12.00 x 10.16 x 4.35 [305 x 258 x 110]	PDF
SCE-12R106	\$151.00	12.00 x 10.16 x 6.35 [305 x 258 x 161]	PDF
SCE-12R124	\$159.00	12.00 x 12.16 x 4.35 [305 x 309 x 110]	PDF
SCE-12R126	\$169.00	12.00 x 12.16 x 6.35 [305 x 309 x 161]	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R Screw Cover Wall-Mount



Dimensions

