

NEMA 3R Vented Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical controls, drives, instruments and components used in an outdoor environment to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects (falling dirt); and provide a degree of protection with respect to the harmful effects on the equipment due to the ingress of water (rain, sleet, snow).

Finish

- White powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R
- cULus Listed Type 3R [File E69392]
- IEC 60529 IP32



Construction

- 14-gauge galvanized steel.
- Black, 1/4-turn latches and padlocking knob
- Provisions for subpanel
- Doors open 180°
- Concealed hinges
- Vented top hood with removable cover and washable reusable filter
- Top mounted fans
- Vented rain hood with filter kits in door
- DIN rail mounting provisions inside top for installation of thermostat and terminals
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body
- Mounting holes for optional mounting straps
- 3/8-16 grounding kit
- Subpanel mounting hardware included
- 115VAC fan
- Provision for lifting lugs is included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm].
 - Lifting lug assembly is included with the enclosure.
- Bolt pack and hole plugs are provided to seal holes in bottom of enclosure.

Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R Vented Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-29VR2412	\$1,006.00	29.00 x 24.00 x 13.07 [737 x 610 x 332]	PDF	SCE-24P24	\$83.00
SCE-29VR2416	\$1,111.00	29.00 x 24.00 x 17.07 [737 x 610 x 434]	PDF	SCE-24P24	\$83.00
SCE-35VR2412	\$1,126.00	35.00 x 24.00 x 13.07 [889 x 610 x 332]	PDF	SCE-30P24	\$98.00
SCE-41VR2412	\$1,273.00	41.00 x 24.00 x 13.07 [1041 x 610 x 332]	PDF	SCE-36P24	\$118.00
SCE-47VR2414	\$1,538.00	47.00 x 24.00 x 15.07 [1194 x 610 x 383]	PDF	SCE-42P24	\$142.00
SCE-53VR3616	\$2,473.00	53.00 x 36.00 x 17.07 [1346 x 914 x 434]	PDF	SCE-48P36	\$240.00
SCE-53VR3620	\$2,753.00	53.00 x 36.00 x 21.07 [1346 x 914 x 535]	PDF	SCE-48P36	\$240.00
SCE-65VR3616	\$2,798.00	65.00 x 36.00 x 17.07 [1651 x 914 x 434]	PDF	SCE-60P36	\$295.00
SCE-65VR3620	\$3,068.00	65.00 x 36.00 x 21.07 [1651 x 914 x 535]	PDF	SCE-60P36	\$295.00

Note: Dimensions in inches [millimeters].

NEMA 3R Vented Single-Door Wall-Mount



Dimensions

