

Enviroline Junction Series

NEMA 3R, 4, 12, and 13

Wall-Mount



Applications

Designed to house electrical controls, instruments, and components in areas, which are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water.

Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinges
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground studs on door and body
- Mounting feet included

Finish

- ANSI 61 gray or RAL7035 gray powder coated inside and out.
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 12, and 13 Wall-Mount

ANSI 61	RAL 7035	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604ELJ	SCE-604ELJLG	\$48.00	6.00 x 4.00 x 4.18 [152 x 102 x 106]	PDF	SCE-6P4	\$4.75
SCE-606ELJ	SCE-606ELJLG	\$56.00	6.00 x 6.00 x 4.18 [152 x 152 x 106]	PDF	SCE-6P6	\$5.50
SCE-806ELJ	SCE-806ELJLG	\$61.00	8.00 x 6.00 x 4.18 [203 x 152 x 106]	PDF	SCE-8P6	\$6.50
SCE-8066ELJ	SCE-8066ELJLG	\$72.00	8.00 x 6.00 x 6.18 [203 x 152 x 157]	PDF	SCE-8P6	\$6.50
SCE-808ELJ	SCE-808ELJLG	\$75.00	8.00 x 8.00 x 4.18 [203 x 203 x 106]	PDF	SCE-8P8	\$7.50
SCE-8086ELJ	SCE-8086ELJLG	\$80.00	8.00 x 8.00 x 6.18 [203 x 203 x 157]	PDF	SCE-8P8	\$7.50
SCE-1008ELJ	SCE-1008ELJLG	\$83.00	10.00 x 8.00 x 4.18 [254 x 203 x 106]	PDF	SCE-10P8	\$8.75
SCE-10086ELJ	SCE-10086ELJLG	\$93.00	10.00 x 8.00 x 6.18 [254 x 203 x 157]	PDF	SCE-10P8	\$8.75
SCE-10106ELJ	SCE-10106ELJLG	\$98.00	10.00 x 10.00 x 6.18 [254 x 254 x 157]	PDF	SCE-10P10	\$10.50
SCE-1210ELJ	SCE-1210ELJLG	\$101.00	12.00 x 10.00 x 6.18 [305 x 254 x 157]	PDF	SCE-12P10	\$12.00
SCE-12108ELJ	SCE-12108ELJLG	\$115.00	12.00 x 10.00 x 8.18 [305 x 254 x 208]	PDF	SCE-12P10	\$12.00
SCE-1212ELJ	SCE-1212ELJLG	\$118.00	12.00 x 12.00 x 6.18 [305 x 305 x 157]	PDF	SCE-12P12	\$14.25
SCE-1412ELJ	SCE-1412ELJLG	\$130.00	14.00 x 12.00 x 6.18 [356 x 305 x 157]	PDF	SCE-14P12	\$15.75
SCE-14128ELJ	SCE-14128ELJLG	\$139.00	14.00 x 12.00 x 8.18 [356 x 305 x 208]	PDF	SCE-14P12	\$15.75
SCE-1614ELJ	SCE-1614ELJLG	\$153.00	16.00 x 14.00 x 6.18 [406 x 356 x 157]	PDF	SCE-16P14	\$31.00
SCE-16148ELJ	SCE-16148ELJLG	\$168.00	16.00 x 14.00 x 8.18 [406 x 356 x 208]	PDF	SCE-16P14	\$31.00
SCE-20166ELJ	SCE-20166ELJLG	\$177.00	20.00 x 16.00 x 6.18 [508 x 406 x 157]	PDF	SCE-20P16J	\$47.50
SCE-20168ELJ	SCE-20168ELJLG	\$185.00	20.00 x 16.00 x 8.18 [508 x 406 x 208]	PDF	SCE-20P16J	\$47.50
SCE-201610ELJ	SCE-201610ELJLG	\$217.00	20.00 x 16.00 x 10.18 [508 x 406 x 259]	PDF	SCE-20P16J	\$47.50
SCE-20206ELJ	SCE-20206ELJLG	\$197.00	20.00 x 20.00 x 6.18 [508 x 508 x 157]	PDF	SCE-20P20J	\$55.00
SCE-20208ELJ	SCE-20208ELJLG	\$208.00	20.00 x 20.00 x 8.18 [508 x 508 x 208]	PDF	SCE-20P20J	\$55.00
SCE-202010ELJ	SCE-202010ELJLG	\$219.00	20.00 x 20.00 x 10.18 [508 x 508 x 259]	PDF	SCE-20P20J	\$55.00

Note: Dimensions in inches [millimeters].