

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor, outdoor and sanitary locations.

Construction

- 14-gauge 304 stainless steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- 15° slope top
- Collar studs are provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers, and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver (optional tamper-resistant latches are available).
- Removable print pocket furnished on enclosures with width greater than 12in [305mm].
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

Options

- Optional mounting feet available
- Door hardware available

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-16EL1208SSST	\$927.00	18.10 x 12.00 x 9.10 [460 x 305 x 231]	PDF	SCE-16P12	\$20.50
SCE-16EL1608SSST	\$1,011.00	18.10 x 16.00 x 9.10 [460 x 406 x 231]	PDF	SCE-16P16	\$34.00
SCE-20EL1608SSST	\$1,132.00	22.10 x 16.00 x 9.10 [561 x 406 x 231]	PDF	SCE-20P16	\$42.00
SCE-20EL1612SSST	\$1,270.00	23.17 x 16.00 x 13.10 [589 x 406 x 333]	PDF	SCE-20P16	\$42.00
SCE-20EL2008SSST	\$1,254.00	22.10 x 20.00 x 9.10 [561 x 508 x 231]	PDF	SCE-20P20	\$49.00
SCE-20EL2012SSST	\$1,600.00	23.17 x 20.00 x 13.10 [589 x 508 x 333]	PDF	SCE-20P20	\$49.00
SCE-24EL2008SSST	\$1,372.00	26.10 x 20.00 x 9.10 [663 x 508 x 231]	PDF	SCE-24P20	\$63.00
SCE-24EL2012SSST	\$1,673.00	27.17 x 20.00 x 13.10 [690 x 508 x 333]	PDF	SCE-24P20	\$63.00
SCE-24EL2408SSST	\$1,507.00	26.10 x 24.00 x 9.10 [663 x 610 x 231]	PDF	SCE-24P24	\$74.00
SCE-24EL2412SSST	\$1,715.00	27.17 x 24.00 x 13.10 [690 x 610 x 333]	PDF	SCE-24P24	\$74.00
SCE-24EL2416SSST	\$2,286.00	28.24 x 24.00 x 17.10 [717 x 610 x 434]	PDF	SCE-24P24	\$74.00
SCE-30EL2408SSST	\$1,715.00	32.10 x 24.00 x 9.10 [815 x 610 x 231]	PDF	SCE-30P24	\$88.00
SCE-30EL2412SSST	\$1,954.00	33.17 x 24.00 x 13.10 [843 x 610 x 333]	PDF	SCE-30P24	\$88.00
SCE-30EL3008SSST	\$1,964.00	32.10 x 30.00 x 9.10 [815 x 762 x 231]	PDF	SCE-30P30	\$116.00
SCE-30EL3012SSST	\$2,442.00	33.17 x 30.00 x 13.10 [843 x 762 x 333]	PDF	SCE-30P30	\$116.00
SCE-36EL2408SSST	\$1,934.00	38.10 x 24.00 x 9.10 [968 x 610 x 231]	PDF	SCE-36P24	\$105.00
SCE-36EL2412SSST	\$2,175.00	39.17 x 24.00 x 13.10 [995 x 610 x 333]	PDF	SCE-36P24	\$105.00
SCE-36EL3008SSST	\$2,197.00	38.10 x 30.00 x 9.10 [968 x 762 x 231]	PDF	SCE-36P30	\$141.00
SCE-36EL3012SSST	\$2,502.00	39.17 x 30.00 x 13.10 [995 x 762 x 333]	PDF	SCE-36P30	\$141.00
SCE-36EL3016SSST	\$2,652.00	40.24 x 30.00 x 17.10 [1022 x 762 x 434]	PDF	SCE-36P30	\$141.00
SCE-36EL3612SSST	\$2,811.00	39.17 x 36.00 x 13.10 [995 x 914 x 333]	PDF	SCE-36P36	\$165.00
SCE-48EL3612SSST	\$3,657.00	51.17 x 36.00 x 13.10 [1300 x 914 x 333]	PDF	SCE-48P36	\$214.00
SCE-48EL3616SSST	\$3,738.00	52.24 x 36.00 x 17.10 [1327 x 914 x 434]	PDF	SCE-48P36	\$214.00
SCE-60EL3612SSST	\$4,183.00	63.17 x 36.00 x 13.10 [1605 x 914 x 333]	PDF	SCE-60P36	\$264.00
SCE-60EL3616SSST	\$4,367.00	64.24 x 36.00 x 17.10 [1632 x 914 x 434]	PDF	SCE-60P36	\$264.00
SCE-60EL4812SSST	\$7,504.00	63.20 x 48.00 x 13.05 [1605 x 1219 x 331]	PDF	SCE-60P48	\$373.00
SCE-60EL4818SSST	\$7,959.00	64.80 x 48.00 x 19.05 [1646 x 1219 x 484]	PDF	SCE-60P48	\$373.00
SCE-60EL6012SSST	\$8,422.00	63.20 x 60.00 x 13.05 [1605 x 1524 x 331]	PDF	SCE-60P60	\$460.00
SCE-60EL6018SSST	\$8,820.00	64.80 x 60.00 x 19.05 [1646 x 1524 x 484]	PDF	SCE-60P60	\$460.00
SCE-72EL6012SSST	\$9,582.00	75.20 x 60.00 x 13.05 [1910 x 1524 x 331]	PDF	SCE-72P60	\$548.00
SCE-72EL6018SSST	\$9,787.00	76.80 x 60.00 x 19.05 [1951 x 1524 x 484]	PDF	SCE-72P60	\$548.00

Note: Dimensions in inches [millimeters].

EnviroLine Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



Your Enclosure Source®

Dimensions

