

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount with 3-Point Handle



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor application a drip shield is recommended.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for all-mounting
- Mounting hardware, sealing washers, and hole plugs are included.
- Concealed hinges
- Removable and interchangeable doors
- Black zinc diecast keylocking/padlocking handles
- 3-point latching mechanism
- Black, 1/4-turn latches, as required
- Removable print pocket
- Oil- and water-resistant gasket
- Ground studs on door and body
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm].
- Lifting lug assembly included with the enclosure bolt pack

Options

- Optional mounting feet available
- Door hardware available

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount with 3-Point Handle

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-24EL2010LPPL	\$499.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$63.00
SCE-24EL2410LPPL	\$527.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$74.00
SCE-30EL2412LPPL	\$591.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$88.00
SCE-30EL3012LPPL	\$661.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$116.00
SCE-36EL2412LPPL	\$638.00	36.00 x 24.00 x 13.10 [914 x 610 x 333]	PDF	SCE-36P24	\$105.00
SCE-36EL3012LPPL	\$697.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$141.00
SCE-42EL3612LPPL	\$819.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$190.00
SCE-48EL3612LPPL	\$880.00	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$214.00
SCE-48EL3616LPPL	\$951.00	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$214.00
SCE-60EL3612LPPL	\$1,001.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$264.00
SCE-60EL3616LPPL	\$1,083.00	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$264.00
SCE-60EL3624LPPL	\$1,531.00	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$264.00
SCE-72EL3624LPPL	\$1,736.00	72.00 x 36.00 x 25.10 [1829 x 914 x 638]	PDF	SCE-72P36	\$313.00

Note: Dimensions in inches [millimeters].