

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Applications

Designed to house electrical and electronic controls, instrumentation and components. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge stainless steel Type 304
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Removable center posts permit easy subpanel installation.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers, and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black, keylocking/padlocking handles
- 3-point latching mechanism
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

Options

- Optional tamper-resistant inserts are available.
- Optional mounting feet are available.
- Door hardware is available.

Note: Mechanical Interlock not for use in enclosures 24.0in [610mm] in height.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

Stainless Steel Enviroline Series Wall-Mount Two-Door Enclosures with 3-Point Handle

| Part Number | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
|-------------------------------------|------------|---|---------------------|-----------------------------|----------|
| SCE-24EL4210SSWFLP | \$3,344.00 | 24.00 x 42.00 x 11.10 [610 x 1067 x 282] | PDF | SCE-42P24 | \$127.00 |
| SCE-24EL4810SSWFLP | \$3,477.00 | 24.00 x 48.00 x 11.10 [610 x 1219 x 282] | PDF | SCE-48P24 | \$137.00 |
| SCE-30EL4210SSWFLP | \$3,544.00 | 30.00 x 42.00 x 11.10 [762 x 1067 x 282] | PDF | SCE-42P30 | \$162.00 |
| SCE-30EL4810SSWFLP | \$3,744.00 | 30.00 x 48.00 x 11.10 [762 x 1219 x 282] | PDF | SCE-48P30 | \$179.00 |
| SCE-30EL6010SSWFLP | \$4,203.00 | 30.00 x 60.00 x 11.10 [762 x 1524 x 282] | PDF | SCE-60P30 | \$221.00 |
| SCE-36EL4212SSWFLP | \$4,219.00 | 36.00 x 42.00 x 13.10 [914 x 1067 x 333] | PDF | SCE-42P36 | \$190.00 |
| SCE-36EL4812SSWFLP | \$4,325.00 | 36.00 x 48.00 x 13.10 [914 x 1219 x 333] | PDF | SCE-48P36 | \$214.00 |
| SCE-36EL6012SSWFLP | \$4,775.00 | 36.00 x 60.00 x 13.10 [914 x 1524 x 333] | PDF | SCE-60P36 | \$264.00 |
| SCE-42EL4212SSWFLP | \$4,277.00 | 42.00 x 42.00 x 13.10 [1067 x 1067 x 333] | PDF | SCE-42P42 | \$218.00 |
| SCE-42EL4812SSWFLP | \$4,751.00 | 42.00 x 48.00 x 13.10 [1067 x 1219 x 333] | PDF | SCE-48P42 | \$246.00 |
| SCE-42EL6012SSWFALP | \$4,989.00 | 42.00 x 60.00 x 13.10 [1067 x 1524 x 333] | PDF | SCE-60BFP42 | \$320.00 |
| SCE-48EL4812SSWFLP | \$4,875.00 | 48.00 x 48.00 x 13.10 [1219 x 1219 x 333] | PDF | SCE-48P48 | \$295.00 |

Note: Dimensions in inches [millimeters].

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Dimensions

