

EnviroLine Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instruments and components in areas which are in very wet conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 14-gauge stainless steel Type 304 or 316L stainless steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Collar studs are provided for mounting optional subpanels.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver (optional tamper-resistant inserts are available).
- Mounting holes in back of enclosure
- Mounting hardware, sealing washers, and hole plugs are included.
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Ground studs on door and body

Options

- Optional mounting feet available (SCE-ELMFK4).
- Door hardware available

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount							
304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-12EL1206SSLP	\$600.00	SCE-12EL1206SS6LP	\$740.00	12.00 x 12.00 x 7.10 [305 x 305 x 180]	PDF	SCE-12DLP12	\$19.00
SCE-12EL2406SSLP	\$797.00	SCE-12EL2406SS6LP	\$983.00	12.00 x 24.00 x 7.10 [305 x 610 x 180]	PDF	SCE-12P24	\$38.50
SCE-16EL1206SSLP	\$660.00	SCE-16EL1206SS6LP	\$814.00	16.00 x 12.00 x 7.10 [406 x 305 x 180]	PDF	SCE-16P12	\$20.50
SCE-16EL1208SSLP	\$706.00	SCE-16EL1208SS6LP	\$871.00	16.00 x 12.00 x 9.10 [406 x 305 x 231]	PDF	SCE-16P12	\$20.50
SCE-16EL1606SSLP	\$732.00	SCE-16EL1606SS6LP	\$903.00	16.00 x 16.00 x 7.10 [406 x 406 x 180]	PDF	SCE-16P16	\$34.00
SCE-16EL1608SSLP	\$770.00	SCE-16EL1608SS6LP	\$949.00	16.00 x 16.00 x 9.10 [406 x 406 x 231]	PDF	SCE-16P16	\$34.00
SCE-16EL2008SSLP	\$862.00	SCE-16EL2008SS6LP	\$1,064.00	16.00 x 20.00 x 9.10 [406 x 508 x 231]	PDF	SCE-20P16	\$42.00
SCE-20EL1606SSLP	\$812.00	SCE-20EL1606SS6LP	\$1,002.00	20.00 x 16.00 x 7.10 [508 x 406 x 180]	PDF	SCE-20P16	\$42.00
SCE-20EL1608SSLP	\$862.00	SCE-20EL1608SS6LP	\$1,064.00	20.00 x 16.00 x 9.10 [508 x 406 x 231]	PDF	SCE-20P16	\$42.00
SCE-20EL1610SSLP	\$920.00	SCE-20EL1610SS6LP	\$1,135.00	20.00 x 16.00 x 11.10 [508 x 406 x 282]	PDF	SCE-20P16	\$42.00
SCE-20EL2006SSLP	\$888.00	SCE-20EL2006SS6LP	\$1,095.00	20.00 x 20.00 x 7.10 [508 x 508 x 180]	PDF	SCE-20P20	\$49.00
SCE-20EL2008SSLP	\$955.00	SCE-20EL2008SS6LP	\$1,178.00	20.00 x 20.00 x 9.10 [508 x 508 x 231]	PDF	SCE-20P20	\$49.00
SCE-20EL2010SSLP	\$1,017.00	SCE-20EL2010SS6LP	\$1,255.00	20.00 x 20.00 x 11.10 [508 x 508 x 282]	PDF	SCE-20P20	\$49.00
SCE-20EL2012SSLP	\$1,218.00	—	—	20.00 x 20.00 x 13.10 [508 x 508 x 333]	PDF	SCE-20P20	\$49.00
SCE-20EL2408SSLP	\$1,045.00	SCE-20EL2408SS6LP	\$1,288.00	20.00 x 24.00 x 9.10 [508 x 610 x 231]	PDF	SCE-24P20	\$63.00
SCE-24EL1608SSLP	\$940.00	SCE-24EL1608SS6LP	\$1,159.00	24.00 x 16.00 x 9.10 [610 x 406 x 231]	PDF	SCE-24P16	\$45.50
SCE-24EL2006SSLP	\$1,024.00	SCE-24EL2006SS6LP	\$1,228.00	24.00 x 20.00 x 7.10 [610 x 508 x 180]	PDF	SCE-24P20	\$63.00
SCE-24EL2008SSLP	\$1,045.00	SCE-24EL2008SS6LP	\$1,288.00	24.00 x 20.00 x 9.10 [610 x 508 x 231]	PDF	SCE-24P20	\$63.00
SCE-24EL2010SSLP	\$1,116.00	SCE-24EL2010SS6LP	\$1,376.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$63.00
SCE-24EL2012SSLP	\$1,274.00	SCE-24EL2012SS6LP	\$1,460.00	24.00 x 20.00 x 13.10 [610 x 508 x 333]	PDF	SCE-24P20	\$63.00
SCE-24EL2408SSLP	\$1,148.00	SCE-24EL2408SS6LP	\$1,416.00	24.00 x 24.00 x 9.10 [610 x 610 x 231]	PDF	SCE-24P24	\$74.00
SCE-24EL2410SSLP	\$1,227.00	SCE-24EL2410SS6LP	\$1,513.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$74.00
SCE-24EL2412SSLP	\$1,306.00	SCE-24EL2412SS6LP	\$1,610.00	24.00 x 24.00 x 13.10 [610 x 610 x 333]	PDF	SCE-24P24	\$74.00
SCE-24EL2416SSLP	\$1,480.00	SCE-24EL2416SS6LP	\$1,826.00	24.00 x 24.00 x 17.10 [610 x 610 x 434]	PDF	SCE-24P24	\$74.00
SCE-24EL3008SSLP	\$1,304.00	SCE-24EL3008SS6LP	\$1,608.00	24.00 x 30.00 x 9.10 [610 x 762 x 231]	PDF	SCE-30P24	\$88.00
SCE-24EL3010SSLP	\$1,403.00	SCE-24EL3010SS6LP	\$1,730.00	24.00 x 30.00 x 11.10 [610 x 762 x 282]	PDF	SCE-30P24	\$88.00
SCE-30EL1606SSLP	\$1,093.00	SCE-30EL1606SS6LP	\$1,348.00	30.00 x 16.00 x 7.10 [762 x 406 x 180]	PDF	SCE-30P16	\$63.00
SCE-30EL2008SSLP	\$1,184.00	SCE-30EL2008SS6LP	\$1,460.00	30.00 x 20.00 x 9.10 [762 x 508 x 231]	PDF	SCE-30P20	\$77.00
SCE-30EL2010SSLP	\$1,283.00	SCE-30EL2010SS6LP	\$1,582.00	30.00 x 20.00 x 11.10 [762 x 508 x 282]	PDF	SCE-30P20	\$77.00
SCE-30EL2408SSLP	\$1,306.00	SCE-30EL2408SS6LP	\$1,610.00	30.00 x 24.00 x 9.10 [762 x 610 x 231]	PDF	SCE-30P24	\$88.00
SCE-30EL2410SSLP	\$1,404.00	SCE-30EL2410SS6LP	\$1,732.00	30.00 x 24.00 x 11.10 [762 x 610 x 282]	PDF	SCE-30P24	\$88.00
SCE-30EL2412SSLP	\$1,488.00	SCE-30EL2412SS6LP	\$1,835.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$88.00
SCE-30EL2416SSLP	\$1,640.00	SCE-30EL2416SS6LP	\$2,022.00	30.00 x 24.00 x 17.10 [762 x 610 x 434]	PDF	SCE-30P24	\$88.00
SCE-30EL3008SSLP	\$1,495.00	SCE-30EL3008SS6LP	\$1,844.00	30.00 x 30.00 x 9.10 [762 x 762 x 231]	PDF	SCE-30P30	\$116.00
SCE-30EL3010SSLP	\$1,586.00	SCE-30EL3010SS6LP	\$1,957.00	30.00 x 30.00 x 11.10 [762 x 762 x 282]	PDF	SCE-30P30	\$116.00
SCE-30EL3012SSLP	\$1,685.00	SCE-30EL3012SS6LP	\$2,078.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$116.00

Note: Dimensions in inches [millimeters].

Table continued on next page

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount							
304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-30EL3608SSLP	\$1,673.00	SCE-30EL3608SS6LP	\$2,063.00	30.00 x 36.00 x 9.10 [762 x 914 x 231]	PDF	SCE-36P30	\$141.00
SCE-36EL2408SSLP	\$1,473.00	SCE-36EL2408SS6LP	\$1,816.00	36.00 x 24.00 x 9.10 [914 x 610 x 231]	PDF	SCE-36P24	\$105.00
SCE-36EL2410SSLP	\$1,571.00	SCE-36EL2410SS6LP	\$1,938.00	36.00 x 24.00 x 11.10 [914 x 610 x 282]	PDF	SCE-36P24	\$105.00
SCE-36EL3008SSLP	\$1,673.00	SCE-36EL3008SS6LP	\$2,063.00	36.00 x 30.00 x 9.10 [914 x 762 x 231]	PDF	SCE-36P30	\$141.00
SCE-36EL3010SSLP	\$1,798.00	SCE-36EL3010SS6LP	\$2,217.00	36.00 x 30.00 x 11.10 [914 x 762 x 282]	PDF	SCE-36P30	\$141.00
SCE-36EL3012SSLP	\$1,905.00	SCE-36EL3012SS6LP	\$2,350.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$141.00
SCE-36EL3016SSLP	\$2,010.00	—	—	36.00 x 30.00 x 17.10 [914 x 762 x 434]	PDF	SCE-36P30	\$141.00
SCE-36EL3608SSLP	\$1,928.00	SCE-36EL3608SS6LP	\$2,378.00	36.00 x 36.00 x 9.10 [914 x 914 x 231]	PDF	SCE-36P36	\$165.00
SCE-36EL3612SSLP	\$2,141.00	SCE-36EL3612SS6LP	\$2,640.00	36.00 x 36.00 x 13.10 [914 x 914 x 333]	PDF	SCE-36P36	\$165.00
SCE-42EL2410SSLP	\$1,822.00	SCE-42EL2410SS6LP	\$2,186.00	42.00 x 24.00 x 11.10 [1067 x 610 x 282]	PDF	SCE-42P24	\$127.00
SCE-42EL3010SSLP	\$1,995.00	SCE-42EL3010SS6LP	\$2,460.00	42.00 x 30.00 x 11.10 [1067 x 762 x 282]	PDF	SCE-42P30	\$162.00
SCE-42EL3012SSLP	\$2,140.00	—	—	42.00 x 30.00 x 13.10 [1067 x 762 x 333]	PDF	SCE-42P30	\$162.00
SCE-42EL3612SSLP	\$2,356.00	SCE-42EL3612SS6LP	\$2,906.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$190.00
SCE-42EL3616SSLP	\$2,502.00	SCE-42EL3616SS6LP	\$3,086.00	42.00 x 36.00 x 17.10 [1067 x 914 x 434]	PDF	SCE-42P36	\$190.00
SCE-48EL2412SSLP	\$2,285.00	—	—	48.00 x 24.00 x 13.10 [1219 x 610 x 333]	PDF	SCE-48P24	\$137.00
SCE-48EL3612SSLP	\$2,611.00	SCE-48EL3612SS6LP	\$3,221.00	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$214.00
SCE-48EL3616SSLP	\$2,847.00	SCE-48EL3616SS6LP	\$3,511.00	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$214.00
SCE-60EL3612SSLP	\$3,082.00	SCE-60EL3612SS6LP	\$3,801.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$264.00
SCE-60EL3616SSLP	\$3,325.00	SCE-60EL3616SS6LP	\$4,101.00	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$264.00
SCE-60EL3624SSLP	\$4,006.00	—	—	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$264.00
SCE-72EL3016SSLP	\$3,568.00	SCE-72EL3016SS6LP	\$4,400.00	72.00 x 30.00 x 17.10 [1829 x 762 x 434]	PDF	SCE-72P30	\$292.00
SCE-72EL3612SSLP	\$3,666.00	SCE-72EL3612SS6LP	\$4,522.00	72.00 x 36.00 x 13.10 [1829 x 914 x 333]	PDF	SCE-72P36	\$313.00
SCE-72EL3616SSLP	\$3,871.00	SCE-72EL3616SS6LP	\$4,775.00	72.00 x 36.00 x 17.10 [1829 x 914 x 434]	PDF	SCE-72P36	\$313.00

Note: Dimensions in inches [millimeters].