

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instruments and components in areas which are in very wet conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 14-gauge stainless steel Type 304 or 316L stainless steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Collar studs are provided for mounting optional subpanels.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver (optional tamper-resistant inserts are available).
- Mounting holes in back of enclosure
- Mounting hardware, sealing washers, and hole plugs are included.
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Ground studs on door and body

Options

- Optional mounting feet available (SCE-ELMFK4).
- Door hardware available

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-12EL1206SSLP	\$496.00	SCE-12EL1206SS6LP	\$589.00	12.00 x 12.00 x 7.10 [305 x 305 x 180]	PDF	SCE-12DLP12	\$21.50
SCE-12EL2406SSLP	\$659.00	SCE-12EL2406SS6LP	\$783.00	12.00 x 24.00 x 7.10 [305 x 610 x 180]	PDF	SCE-12P24	\$43.50
SCE-16EL1206SSLP	\$546.00	SCE-16EL1206SS6LP	\$649.00	16.00 x 12.00 x 7.10 [406 x 305 x 180]	PDF	SCE-16P12	\$23.00
SCE-16EL1208SSLP	\$583.00	SCE-16EL1208SS6LP	\$693.00	16.00 x 12.00 x 9.10 [406 x 305 x 231]	PDF	SCE-16P12	\$23.00
SCE-16EL1606SSLP	\$605.00	SCE-16EL1606SS6LP	\$719.00	16.00 x 16.00 x 7.10 [406 x 406 x 180]	PDF	SCE-16P16	\$38.00
SCE-16EL1608SSLP	\$636.00	SCE-16EL1608SS6LP	\$756.00	16.00 x 16.00 x 9.10 [406 x 406 x 231]	PDF	SCE-16P16	\$38.00
SCE-16EL2008SSLP	\$713.00	SCE-16EL2008SS6LP	\$847.00	16.00 x 20.00 x 9.10 [406 x 508 x 231]	PDF	SCE-20P16	\$47.00
SCE-20EL1606SSLP	\$671.00	SCE-20EL1606SS6LP	\$798.00	20.00 x 16.00 x 7.10 [508 x 406 x 180]	PDF	SCE-20P16	\$47.00
SCE-20EL1608SSLP	\$713.00	SCE-20EL1608SS6LP	\$847.00	20.00 x 16.00 x 9.10 [508 x 406 x 231]	PDF	SCE-20P16	\$47.00
SCE-20EL1610SSLP	\$760.00	SCE-20EL1610SS6LP	\$904.00	20.00 x 16.00 x 11.10 [508 x 406 x 282]	PDF	SCE-20P16	\$47.00
SCE-20EL2006SSLP	\$734.00	SCE-20EL2006SS6LP	\$872.00	20.00 x 20.00 x 7.10 [508 x 508 x 180]	PDF	SCE-20P20	\$55.00
SCE-20EL2008SSLP	\$789.00	SCE-20EL2008SS6LP	\$938.00	20.00 x 20.00 x 9.10 [508 x 508 x 231]	PDF	SCE-20P20	\$55.00
SCE-20EL2010SSLP	\$841.00	SCE-20EL2010SS6LP	\$999.00	20.00 x 20.00 x 11.10 [508 x 508 x 282]	PDF	SCE-20P20	\$55.00
SCE-20EL2012SSLP	\$1,007.00	—	—	20.00 x 20.00 x 13.10 [508 x 508 x 333]	PDF	SCE-20P20	\$55.00
SCE-20EL2408SSLP	\$863.00	SCE-20EL2408SS6LP	\$1,026.00	20.00 x 24.00 x 9.10 [508 x 610 x 231]	PDF	SCE-24P20	\$71.00
SCE-24EL1608SSLP	\$777.00	SCE-24EL1608SS6LP	\$923.00	24.00 x 16.00 x 9.10 [610 x 406 x 231]	PDF	SCE-24P16	\$51.00
SCE-24EL2006SSLP	\$846.00	SCE-24EL2006SS6LP	\$978.00	24.00 x 20.00 x 7.10 [610 x 508 x 180]	PDF	SCE-24P20	\$71.00
SCE-24EL2008SSLP	\$863.00	SCE-24EL2008SS6LP	\$1,026.00	24.00 x 20.00 x 9.10 [610 x 508 x 231]	PDF	SCE-24P20	\$71.00
SCE-24EL2010SSLP	\$922.00	SCE-24EL2010SS6LP	\$1,096.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$71.00
SCE-24EL2012SSLP	\$1,053.00	SCE-24EL2012SS6LP	\$1,163.00	24.00 x 20.00 x 13.10 [610 x 508 x 333]	PDF	SCE-24P20	\$71.00
SCE-24EL2408SSLP	\$948.00	SCE-24EL2408SS6LP	\$1,127.00	24.00 x 24.00 x 9.10 [610 x 610 x 231]	PDF	SCE-24P24	\$83.00
SCE-24EL2410SSLP	\$1,014.00	SCE-24EL2410SS6LP	\$1,205.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$83.00
SCE-24EL2412SSLP	\$1,079.00	SCE-24EL2412SS6LP	\$1,283.00	24.00 x 24.00 x 13.10 [610 x 610 x 333]	PDF	SCE-24P24	\$83.00
SCE-24EL2416SSLP	\$1,365.00	SCE-24EL2416SS6LP	\$1,619.00	24.00 x 24.00 x 17.10 [610 x 610 x 434]	PDF	SCE-24P24	\$83.00
SCE-24EL3008SSLP	\$1,078.00	SCE-24EL3008SS6LP	\$1,281.00	24.00 x 30.00 x 9.10 [610 x 762 x 231]	PDF	SCE-30P24	\$98.00
SCE-24EL3010SSLP	\$1,159.00	SCE-24EL3010SS6LP	\$1,378.00	24.00 x 30.00 x 11.10 [610 x 762 x 282]	PDF	SCE-30P24	\$98.00
SCE-30EL1606SSLP	\$903.00	SCE-30EL1606SS6LP	\$1,074.00	30.00 x 16.00 x 7.10 [762 x 406 x 180]	PDF	SCE-30P16	\$71.00
SCE-30EL2008SSLP	\$979.00	SCE-30EL2008SS6LP	\$1,163.00	30.00 x 20.00 x 9.10 [762 x 508 x 231]	PDF	SCE-30P20	\$87.00
SCE-30EL2010SSLP	\$1,060.00	SCE-30EL2010SS6LP	\$1,260.00	30.00 x 20.00 x 11.10 [762 x 508 x 282]	PDF	SCE-30P20	\$87.00
SCE-30EL2408SSLP	\$1,079.00	SCE-30EL2408SS6LP	\$1,283.00	30.00 x 24.00 x 9.10 [762 x 610 x 231]	PDF	SCE-30P24	\$98.00
SCE-30EL2410SSLP	\$1,160.00	SCE-30EL2410SS6LP	\$1,380.00	30.00 x 24.00 x 11.10 [762 x 610 x 282]	PDF	SCE-30P24	\$98.00
SCE-30EL2412SSLP	\$1,229.00	SCE-30EL2412SS6LP	\$1,462.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$98.00
SCE-30EL2416SSLP	\$1,482.00	SCE-30EL2416SS6LP	\$1,763.00	30.00 x 24.00 x 17.10 [762 x 610 x 434]	PDF	SCE-30P24	\$98.00
SCE-30EL3008SSLP	\$1,376.00	SCE-30EL3008SS6LP	\$1,633.00	30.00 x 30.00 x 9.10 [762 x 762 x 231]	PDF	SCE-30P30	\$130.00
SCE-30EL3010SSLP	\$1,443.00	SCE-30EL3010SS6LP	\$1,715.00	30.00 x 30.00 x 11.10 [762 x 762 x 282]	PDF	SCE-30P30	\$130.00
SCE-30EL3012SSLP	\$1,516.00	SCE-30EL3012SS6LP	\$1,804.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$130.00

Note: Dimensions in inches [millimeters].

Table continued on next page

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount							
304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-30EL3608SSLP	\$1,507.00	SCE-30EL3608SS6LP	\$1,793.00	30.00 x 36.00 x 9.10 [762 x 914 x 231]	PDF	SCE-36P30	\$157.00
SCE-36EL2408SSLP	\$1,359.00	SCE-36EL2408SS6LP	\$1,612.00	36.00 x 24.00 x 9.10 [914 x 610 x 231]	PDF	SCE-36P24	\$118.00
SCE-36EL2410SSLP	\$1,432.00	SCE-36EL2410SS6LP	\$1,701.00	36.00 x 24.00 x 11.10 [914 x 610 x 282]	PDF	SCE-36P24	\$118.00
SCE-36EL3008SSLP	\$1,507.00	SCE-36EL3008SS6LP	\$1,793.00	36.00 x 30.00 x 9.10 [914 x 762 x 231]	PDF	SCE-36P30	\$157.00
SCE-36EL3010SSLP	\$1,598.00	SCE-36EL3010SS6LP	\$1,906.00	36.00 x 30.00 x 11.10 [914 x 762 x 282]	PDF	SCE-36P30	\$157.00
SCE-36EL3012SSLP	\$1,677.00	SCE-36EL3012SS6LP	\$2,004.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$157.00
SCE-36EL3016SSLP	\$1,754.00	—	—	36.00 x 30.00 x 17.10 [914 x 762 x 434]	PDF	SCE-36P30	\$157.00
SCE-36EL3608SSLP	\$1,694.00	SCE-36EL3608SS6LP	\$2,025.00	36.00 x 36.00 x 9.10 [914 x 914 x 231]	PDF	SCE-36P36	\$185.00
SCE-36EL3612SSLP	\$1,850.00	SCE-36EL3612SS6LP	\$2,217.00	36.00 x 36.00 x 13.10 [914 x 914 x 333]	PDF	SCE-36P36	\$185.00
SCE-42EL2410SSLP	\$1,616.00	SCE-42EL2410SS6LP	\$1,884.00	42.00 x 24.00 x 11.10 [1067 x 610 x 282]	PDF	SCE-42P24	\$142.00
SCE-42EL3010SSLP	\$1,743.00	SCE-42EL3010SS6LP	\$2,085.00	42.00 x 30.00 x 11.10 [1067 x 762 x 282]	PDF	SCE-42P30	\$181.00
SCE-42EL3012SSLP	\$1,850.00	—	—	42.00 x 30.00 x 13.10 [1067 x 762 x 333]	PDF	SCE-42P30	\$181.00
SCE-42EL3612SSLP	\$2,009.00	SCE-42EL3612SS6LP	\$2,412.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$213.00
SCE-42EL3616SSLP	\$2,116.00	SCE-42EL3616SS6LP	\$2,544.00	42.00 x 36.00 x 17.10 [1067 x 914 x 434]	PDF	SCE-42P36	\$213.00
SCE-48EL2412SSLP	\$1,956.00	—	—	48.00 x 24.00 x 13.10 [1219 x 610 x 333]	PDF	SCE-48P24	\$154.00
SCE-48EL3612SSLP	\$2,196.00	SCE-48EL3612SS6LP	\$2,643.00	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$240.00
SCE-48EL3616SSLP	\$2,369.00	SCE-48EL3616SS6LP	\$2,857.00	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$240.00
SCE-60EL3612SSLP	\$2,547.00	SCE-60EL3612SS6LP	\$3,070.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$295.00
SCE-60EL3616SSLP	\$2,748.00	SCE-60EL3616SS6LP	\$3,290.00	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$295.00
SCE-60EL3624SSLP	\$3,310.00	—	—	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$295.00
SCE-72EL3016SSLP	\$2,948.00	SCE-72EL3016SS6LP	\$3,510.00	72.00 x 30.00 x 17.10 [1829 x 762 x 434]	PDF	SCE-72P30	\$327.00
SCE-72EL3612SSLP	\$3,030.00	SCE-72EL3612SS6LP	\$3,602.00	72.00 x 36.00 x 13.10 [1829 x 914 x 333]	PDF	SCE-72P36	\$350.00
SCE-72EL3616SSLP	\$3,199.00	SCE-72EL3616SS6LP	\$3,803.00	72.00 x 36.00 x 17.10 [1829 x 914 x 434]	PDF	SCE-72P36	\$350.00

Note: Dimensions in inches [millimeters].