

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle



Your Enclosure Source®



## Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor applications a drip shield is recommended.

## Construction

- 14-gauge stainless steel Type 304 or 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black zinc diecast keylocking/padlocking handles
- 3-point latching mechanism
- Black, 1/4-turn latches, as required
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

## Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

## Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-24EL2010SSLPPL</a>	\$1,241.00	<a href="#">SCE-24EL2010SS6LPPL</a>	\$1,530.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	\$63.00
<a href="#">SCE-24EL2410SSLPPL</a>	\$1,350.00	<a href="#">SCE-24EL2410SS6LPPL</a>	\$1,666.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	\$74.00
<a href="#">SCE-30EL2412SSLPPL</a>	\$1,612.00	<a href="#">SCE-30EL2412SS6LPPL</a>	\$1,988.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	\$88.00
<a href="#">SCE-36EL2412SSLPPL</a>	\$1,786.00	<a href="#">SCE-30EL3012SS6LPPL</a>	\$2,229.00	36.00 x 24.00 x 13.10 [914 x 610 x 333]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	\$105.00
<a href="#">SCE-30EL3012SSLPPL</a>	\$1,808.00	<a href="#">SCE-36EL3012SS6LPPL</a>	\$2,502.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	<a href="#">PDF</a>	<a href="#">SCE-30P30</a>	\$116.00
<a href="#">SCE-36EL3012SSLPPL</a>	\$2,028.00	<a href="#">SCE-36EL2412SS6LPPL</a>	\$2,203.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	\$141.00
<a href="#">SCE-36EL3612SSLPPL</a>	\$2,283.00	—	—	36.00 x 36.00 x 13.10 [914 x 914 x 333]	<a href="#">PDF</a>	<a href="#">SCE-36P36</a>	\$165.00
<a href="#">SCE-42EL3612SSLPPL</a>	\$2,470.00	<a href="#">SCE-42EL3612SS6LPPL</a>	\$3,046.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	<a href="#">PDF</a>	<a href="#">SCE-42P36</a>	\$190.00
<a href="#">SCE-48EL3612SSLPPL</a>	\$2,725.00	—	—	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	\$214.00
<a href="#">SCE-48EL3616SSLPPL</a>	\$2,972.00	—	—	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	\$214.00
<a href="#">SCE-60EL3612SSLPPL</a>	\$3,194.00	<a href="#">SCE-60EL3612SS6LPPL</a>	\$3,939.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	\$264.00
<a href="#">SCE-60EL3616SSLPPL</a>	\$3,446.00	—	—	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	\$264.00
<a href="#">SCE-60EL3624SSLPPL</a>	\$4,120.00	—	—	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	\$264.00
<a href="#">SCE-72EL3624SSLPPL</a>	\$5,008.00	—	—	72.00 x 36.00 x 25.10 [1829 x 914 x 638]	<a href="#">PDF</a>	<a href="#">SCE-72P36</a>	\$313.00

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle



## Dimensions

