

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge stainless steel Type 304 or 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black zinc diecast keylocking/padlocking handles
- 3-point latching mechanism
- Black, 1/4-turn latches, as required
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-24EL2010SSLPPL	\$1,025.00	SCE-24EL2010SS6LPPL	\$1,219.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$71.00
SCE-24EL2410SSLPPL	\$1,116.00	SCE-24EL2410SS6LPPL	\$1,327.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$83.00
SCE-30EL2412SSLPPL	\$1,462.00	SCE-30EL2412SS6LPPL	\$1,738.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$98.00
SCE-36EL2412SSLPPL	\$1,590.00	SCE-30EL3012SS6LPPL	\$1,915.00	36.00 x 24.00 x 13.10 [914 x 610 x 333]	PDF	SCE-36P24	\$118.00
SCE-30EL3012SSLPPL	\$1,606.00	SCE-36EL3012SS6LPPL	\$2,115.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$130.00
SCE-36EL3012SSLPPL	\$1,768.00	SCE-36EL2412SS6LPPL	\$1,896.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$157.00
SCE-36EL3612SSLPPL	\$1,955.00	—	—	36.00 x 36.00 x 13.10 [914 x 914 x 333]	PDF	SCE-36P36	\$185.00
SCE-42EL3612SSLPPL	\$2,092.00	SCE-42EL3612SS6LPPL	\$2,515.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$213.00
SCE-48EL3612SSLPPL	\$2,279.00	—	—	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$240.00
SCE-48EL3616SSLPPL	\$2,461.00	—	—	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$240.00
SCE-60EL3612SSLPPL	\$2,640.00	SCE-60EL3612SS6LPPL	\$3,172.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$295.00
SCE-60EL3616SSLPPL	\$2,848.00	—	—	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$295.00
SCE-60EL3624SSLPPL	\$3,405.00	—	—	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$295.00
SCE-72EL3624SSLPPL	\$4,139.00	—	—	72.00 x 36.00 x 25.10 [1829 x 914 x 638]	PDF	SCE-72P36	\$350.00

Note: Dimensions in inches [millimeters].

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with 3-Point Handle



Your Enclosure Source®

Dimensions

