

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



Your Enclosure Source®



Applications

Designed to house electrical controls, instruments, and components in areas which may be regularly hosed down or are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water.

Construction

- 16-gauge stainless steel Type 304 stainless steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinge
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet are included.
- 10° slope top

Note: Recommend use as NEMA 3R in cULus outdoor exposure and extreme weather environments.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Slope Top

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604ELJSSST	\$356.00	6.51 x 4.00 x 4.18 [165 x 102 x 106]	PDF	SCE-6P4	\$4.25
SCE-606ELJSSST	\$444.00	6.51 x 6.00 x 4.18 [165 x 152 x 106]	PDF	SCE-6P6	\$5.00
SCE-806ELJSSST	\$464.00	8.51 x 6.00 x 4.18 [216 x 152 x 106]	PDF	SCE-8P6	\$5.75
SCE-8066ELJSSST	\$530.00	8.87 x 6.00 x 6.18 [225 x 152 x 157]	PDF	SCE-8P6	\$5.75
SCE-1008ELJSSST	\$671.00	10.51 x 8.00 x 4.18 [267 x 203 x 106]	PDF	SCE-10P8	\$8.00
SCE-10086ELJSSST	\$747.00	10.87 x 8.00 x 6.18 [276 x 203 x 157]	PDF	SCE-10P8	\$8.00
SCE-1210ELJSSST	\$776.00	12.87 x 10.00 x 6.18 [327 x 254 x 157]	PDF	SCE-12P10	\$10.75
SCE-12108ELJSSST	\$833.00	13.22 x 10.00 x 8.18 [336 x 254 x 208]	PDF	SCE-12P10	\$10.75
SCE-1212ELJSSST	\$839.00	12.87 x 12.00 x 6.18 [327 x 305 x 157]	PDF	SCE-12P12	\$12.50
SCE-14128ELJSSST	\$946.00	15.22 x 12.00 x 8.18 [387 x 305 x 208]	PDF	SCE-14P12	\$14.00
SCE-16148ELJSSST	\$987.00	17.22 x 14.00 x 8.18 [437 x 356 x 208]	PDF	SCE-16P14	\$27.50

Note: Dimensions in inches [millimeters].