

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Window



Applications

Designed to house electrical controls, instruments, and components that require unrestricted viewing of the gauges or controls, in areas which are in wet or oily conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 16-gauge stainless steel Type 304 or 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- 0.25 in [6mm] polycarbonate viewing window
- Standoffs provided for mounting optional subpanels
- Removable hinge
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet are included.
- Optional latches are available.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Note: Recommend use as NEMA 3R in cULus outdoor exposure and extreme weather environments.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Window

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-1008ELJWSS	\$398.00	SCE-1008ELJWSS6	\$496.00	10.00 x 8.00 x 4.18 [254 x 203 x 106]	PDF	SCE-10P8	\$8.00
SCE-10086ELJWSS	\$420.00	SCE-10086ELJWSS6	\$523.00	10.00 x 8.00 x 6.18 [254 x 203 x 157]	PDF	SCE-10P8	\$8.00
SCE-12108ELJWSS	\$479.00	SCE-12108ELJWSS6	\$596.00	12.00 x 10.00 x 6.18 [305 x 254 x 157]	PDF	SCE-12P10	\$10.75
SCE-1210ELJWSS	\$463.00	SCE-1210ELJWSS6	\$577.00	12.00 x 10.00 x 8.18 [305 x 254 x 208]	PDF	SCE-12P10	\$10.75
SCE-16148ELJWSS	\$662.00	SCE-16148ELJWSS6	\$824.00	16.00 x 14.00 x 6.18 [406 x 356 x 157]	PDF	SCE-16P14	\$27.50
SCE-1614ELJWSS	\$625.00	SCE-1614ELJWSS6	\$778.00	16.00 x 14.00 x 8.18 [406 x 356 x 208]	PDF	SCE-16P14	\$27.50

Note: Dimensions in inches [millimeters].