

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical controls, instruments, and components in areas, which are in very wet or oily conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 16-gauge stainless steel Type 304 or 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinge
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet are included.
- Optional latches are available.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604ELJSS	\$150.00	SCE-604ELJSS6	\$187.00	6.00 x 4.00 x 4.18 [152 x 102 x 106]	PDF	SCE-6P4	\$4.25
SCE-606ELJSS	\$188.00	SCE-606ELJSS6	\$234.00	6.00 x 6.00 x 4.18 [152 x 152 x 106]	PDF	SCE-6P6	\$5.00
SCE-806ELJSS	\$196.00	SCE-806ELJSS6	\$244.00	8.00 x 6.00 x 4.18 [203 x 152 x 106]	PDF	SCE-8P6	\$5.75
SCE-8066ELJSS	\$224.00	SCE-8066ELJSS6	\$279.00	8.00 x 6.00 x 6.18 [203 x 152 x 157]	PDF	SCE-8P6	\$5.75
SCE-1008ELJSS	\$289.00	SCE-1008ELJSS6	\$360.00	10.00 x 8.00 x 4.18 [254 x 203 x 106]	PDF	SCE-10P8	\$8.00
SCE-10086ELJSS	\$322.00	SCE-10086ELJSS6	\$401.00	10.00 x 8.00 x 6.18 [254 x 203 x 157]	PDF	SCE-10P8	\$8.00
SCE-1210ELJSS	\$364.00	SCE-1210ELJSS6	\$454.00	12.00 x 10.00 x 6.18 [305 x 254 x 157]	PDF	SCE-12P10	\$10.75
SCE-12108ELJSS	\$391.00	SCE-12108ELJSS6	\$487.00	12.00 x 10.00 x 8.18 [305 x 254 x 208]	PDF	SCE-12P10	\$10.75
SCE-1212ELJSS	\$394.00	SCE-1212ELJSS6	\$490.00	12.00 x 12.00 x 6.18 [305 x 305 x 157]	PDF	SCE-12P12	\$12.50
SCE-1412ELJSS	\$419.00	SCE-1412ELJSS6	\$522.00	14.00 x 12.00 x 6.18 [356 x 305 x 157]	PDF	SCE-14P12	\$14.00
SCE-14128ELJSS	\$444.00	SCE-14128ELJSS6	\$553.00	14.00 x 12.00 x 8.18 [356 x 305 x 208]	PDF	SCE-14P12	\$14.00
SCE-1614ELJSS	\$493.00	SCE-1614ELJSS6	\$614.00	16.00 x 14.00 x 6.18 [406 x 356 x 157]	PDF	SCE-16P14	\$27.50
SCE-16148ELJSS	\$563.00	SCE-16148ELJSS6	\$701.00	16.00 x 14.00 x 8.18 [406 x 356 x 208]	PDF	SCE-16P14	\$27.50

Note: Dimensions in inches [millimeters].