

IP69K Sanitary Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to withstand high pressure and high-temperature wash down procedures with direct and indirect food contact applications within the food and beverage industry. Enclosure is designed with internal swing-out hinges to reduce bacteria catch points and helps to maximize back panel space.

Includes dual gasket design that ensures performance in extreme applications. FDA-grade silicone gasket helps resist bacterial growth and chemical absorption.

Construction

- 14-gauge 304 stainless steel
- Seams continuously welded and ground smooth
- 15° slope top
- Internal swing out hinges
- Doors open 110°
- Stainless sanitary quarter turn latches with FDA-grade silicone gasket
- Poured-in-place oil- and water-resistant gasket
- FDA-grade silicone outer gasket
- Provision for mounting optional panels
- Mounting holes in back of enclosure for optional mounting stand-off or other mounting options
- Ground stud on door and body

Finish

- # 4 Brushed finish 25-35 RA suitable for medical and food industry.

Listings

- NEMA Type 3R, 4, 4X, and 12
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP69K
- ANSI/NSF 169



IP69K Sanitary Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

IP69K Sanitary Stainless Steel Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-16K1208SSST	\$1,191.00	18.10 x 12.00 x 9.10 [460 x 305 x 231]	PDF	SCE-16P12	\$23.00
SCE-16K1608SSST	\$1,295.00	18.10 x 16.00 x 9.10 [460 x 406 x 231]	PDF	SCE-16P16	\$38.00
SCE-20K1608SSST	\$1,445.00	22.10 x 16.00 x 9.10 [561 x 406 x 231]	PDF	SCE-20P16	\$47.00
SCE-20K2008SSST	\$1,596.00	22.10 x 20.00 x 9.10 [561 x 508 x 231]	PDF	SCE-20P20	\$55.00
SCE-20K2010SSST	\$1,646.00	22.64 x 20.00 x 11.10 [575 x 508 x 282]	PDF	SCE-20P20	\$55.00
SCE-24K2008SSST	\$1,742.00	26.10 x 20.00 x 9.10 [663 x 508 x 231]	PDF	SCE-24P20	\$71.00
SCE-24K2010SSST	\$1,768.00	26.64 x 20.00 x 11.10 [677 x 508 x 282]	PDF	SCE-24P20	\$71.00
SCE-24K2012SSST	\$1,969.00	27.17 x 20.00 x 13.10 [690 x 508 x 333]	PDF	SCE-24P20	\$71.00
SCE-24K2408SSST	\$1,910.00	26.10 x 24.00 x 9.10 [663 x 610 x 231]	PDF	SCE-24P24	\$83.00
SCE-24K2410SSST	\$1,911.00	26.64 x 24.00 x 11.10 [677 x 610 x 282]	PDF	SCE-24P24	\$83.00
SCE-24K2412SSST	\$2,167.00	27.17 x 24.00 x 13.10 [690 x 610 x 333]	PDF	SCE-24P24	\$83.00
SCE-30K2408SSST	\$2,167.00	32.10 x 24.00 x 9.10 [815 x 610 x 231]	PDF	SCE-30P24	\$98.00
SCE-30K2412SSST	\$2,464.00	33.17 x 24.00 x 13.10 [843 x 610 x 333]	PDF	SCE-30P24	\$98.00
SCE-30K3012SSST	\$3,069.00	33.17 x 30.00 x 13.10 [843 x 762 x 333]	PDF	SCE-30P30	\$130.00
SCE-36K2412SSST	\$2,755.00	39.17 x 24.00 x 13.10 [995 x 610 x 333]	PDF	SCE-36P24	\$118.00
SCE-36K3012SSST	\$3,161.00	39.17 x 30.00 x 13.10 [995 x 762 x 333]	PDF	SCE-36P30	\$157.00
SCE-36K3016SSST	\$3,348.00	40.24 x 30.00 x 17.10 [1022 x 762 x 434]	PDF	SCE-36P30	\$157.00
SCE-42K3612SSST	\$3,507.00	45.17 x 36.00 x 13.10 [1147 x 914 x 333]	PDF	SCE-42P36	\$213.00
SCE-42K3616SSST	\$3,724.00	46.24 x 36.00 x 17.10 [1174 x 914 x 434]	PDF	SCE-42P36	\$213.00
SCE-48K3612SSST	\$4,601.00	51.17 x 36.00 x 13.10 [1300 x 914 x 333]	PDF	SCE-48P36	\$240.00
SCE-48K3616SSST	\$4,702.00	52.24 x 36.00 x 17.10 [1327 x 914 x 434]	PDF	SCE-48P36	\$240.00

Note: Dimensions in inches [millimeters].