

# IP69K Sanitary Stainless Steel Single-Door Wall-Mount



*Your Enclosure Source®*



## Applications

Designed to withstand high pressure and high-temperature wash down procedures with direct and indirect food contact applications within the food and beverage industry. Enclosure is designed with internal swing-out hinges to reduce bacteria catch points and helps to maximize back panel space.

Includes dual gasket design that ensures performance in extreme applications. FDA-grade silicone gasket helps resist bacterial growth and chemical absorption.

## Construction

- 14-gauge 304 stainless steel
- Seams continuously welded and ground smooth
- 15° slope top
- Internal swing out hinges
- Doors open 110°
- Stainless sanitary quarter turn latches with FDA-grade silicone gasket
- Poured-in-place oil- and water-resistant gasket
- FDA-grade silicone outer gasket
- Provision for mounting optional panels
- Mounting holes in back of enclosure for optional mounting stand-off or other mounting options
- Ground stud on door and body

## Finish

- # 4 Brushed finish 25-35 RA suitable for medical and food industry.

## Listings

- NEMA Type 3R, 4, 4X, and 12
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP69K
- ANSI/NSF 169



# IP69K Sanitary Stainless Steel Single-Door Wall-Mount



## Shipping Schedule

|          |             |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

## IP69K Sanitary Stainless Steel Single-Door Wall-Mount

| Part Number                     | Price      | Size<br>HxWxD                            | Drawing<br>Link     | Optional Subpanel         | Price    |
|---------------------------------|------------|------------------------------------------|---------------------|---------------------------|----------|
| <a href="#">SCE-16K1208SSST</a> | \$1,191.00 | 18.10 x 12.00 x 9.10 [460 x 305 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-16P12</a> | \$23.00  |
| <a href="#">SCE-16K1608SSST</a> | \$1,295.00 | 18.10 x 16.00 x 9.10 [460 x 406 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-16P16</a> | \$38.00  |
| <a href="#">SCE-20K1608SSST</a> | \$1,445.00 | 22.10 x 16.00 x 9.10 [561 x 406 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-20P16</a> | \$47.00  |
| <a href="#">SCE-20K2008SSST</a> | \$1,596.00 | 22.10 x 20.00 x 9.10 [561 x 508 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-20P20</a> | \$55.00  |
| <a href="#">SCE-20K2010SSST</a> | \$1,646.00 | 22.64 x 20.00 x 11.10 [575 x 508 x 282]  | <a href="#">PDF</a> | <a href="#">SCE-20P20</a> | \$55.00  |
| <a href="#">SCE-24K2008SSST</a> | \$1,742.00 | 26.10 x 20.00 x 9.10 [663 x 508 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-24P20</a> | \$71.00  |
| <a href="#">SCE-24K2010SSST</a> | \$1,768.00 | 26.64 x 20.00 x 11.10 [677 x 508 x 282]  | <a href="#">PDF</a> | <a href="#">SCE-24P20</a> | \$71.00  |
| <a href="#">SCE-24K2012SSST</a> | \$1,969.00 | 27.17 x 20.00 x 13.10 [690 x 508 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-24P20</a> | \$71.00  |
| <a href="#">SCE-24K2408SSST</a> | \$1,910.00 | 26.10 x 24.00 x 9.10 [663 x 610 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-24P24</a> | \$83.00  |
| <a href="#">SCE-24K2410SSST</a> | \$1,911.00 | 26.64 x 24.00 x 11.10 [677 x 610 x 282]  | <a href="#">PDF</a> | <a href="#">SCE-24P24</a> | \$83.00  |
| <a href="#">SCE-24K2412SSST</a> | \$2,167.00 | 27.17 x 24.00 x 13.10 [690 x 610 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-24P24</a> | \$83.00  |
| <a href="#">SCE-30K2408SSST</a> | \$2,167.00 | 32.10 x 24.00 x 9.10 [815 x 610 x 231]   | <a href="#">PDF</a> | <a href="#">SCE-30P24</a> | \$98.00  |
| <a href="#">SCE-30K2412SSST</a> | \$2,464.00 | 33.17 x 24.00 x 13.10 [843 x 610 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-30P24</a> | \$98.00  |
| <a href="#">SCE-30K3012SSST</a> | \$3,069.00 | 33.17 x 30.00 x 13.10 [843 x 762 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-30P30</a> | \$130.00 |
| <a href="#">SCE-36K2412SSST</a> | \$2,755.00 | 39.17 x 24.00 x 13.10 [995 x 610 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-36P24</a> | \$118.00 |
| <a href="#">SCE-36K3012SSST</a> | \$3,161.00 | 39.17 x 30.00 x 13.10 [995 x 762 x 333]  | <a href="#">PDF</a> | <a href="#">SCE-36P30</a> | \$157.00 |
| <a href="#">SCE-36K3016SSST</a> | \$3,348.00 | 40.24 x 30.00 x 17.10 [1022 x 762 x 434] | <a href="#">PDF</a> | <a href="#">SCE-36P30</a> | \$157.00 |
| <a href="#">SCE-42K3612SSST</a> | \$3,507.00 | 45.17 x 36.00 x 13.10 [1147 x 914 x 333] | <a href="#">PDF</a> | <a href="#">SCE-42P36</a> | \$213.00 |
| <a href="#">SCE-42K3616SSST</a> | \$3,724.00 | 46.24 x 36.00 x 17.10 [1174 x 914 x 434] | <a href="#">PDF</a> | <a href="#">SCE-42P36</a> | \$213.00 |
| <a href="#">SCE-48K3612SSST</a> | \$4,601.00 | 51.17 x 36.00 x 13.10 [1300 x 914 x 333] | <a href="#">PDF</a> | <a href="#">SCE-48P36</a> | \$240.00 |
| <a href="#">SCE-48K3616SSST</a> | \$4,702.00 | 52.24 x 36.00 x 17.10 [1327 x 914 x 434] | <a href="#">PDF</a> | <a href="#">SCE-48P36</a> | \$240.00 |

Note: Dimensions in inches [millimeters].