

# NEMA 1 Wire Trough



Your Enclosure Source®



## Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust tight protection.

## Construction

- 16-gauge or 18-gauge carbon steel, depending on size
  - See drawings for details
- Spot weld construction
- Standoffs are provided for mounting optional subpanels.
- Removable cover
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body
- Mounting holes in back of enclosure
- Tamper-resistant 1/4-turn latches available

## Finish

- ANSI 61 gray powder coated inside and out

## Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### NEMA 1 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link
<a href="#">SCE-L9N126LP</a>	\$203.00	9.00 x 12.00 x 6.18 [229 x 305 x 157]	<a href="#">PDF</a>
<a href="#">SCE-L9N128LP</a>	\$215.00	9.00 x 12.00 x 8.18 [229 x 305 x 208]	<a href="#">PDF</a>
<a href="#">SCE-L9N186LP</a>	\$204.00	9.00 x 18.00 x 6.18 [229 x 457 x 157]	<a href="#">PDF</a>
<a href="#">SCE-L9N188LP</a>	\$217.00	9.00 x 18.00 x 8.18 [229 x 457 x 208]	<a href="#">PDF</a>
<a href="#">SCE-L9N246LP</a>	\$211.00	9.00 x 24.00 x 6.18 [229 x 610 x 157]	<a href="#">PDF</a>
<a href="#">SCE-L9N248LP</a>	\$223.00	9.00 x 24.00 x 8.18 [229 x 610 x 208]	<a href="#">PDF</a>
<a href="#">SCE-L9N306LP</a>	\$212.00	9.00 x 30.00 x 6.18 [229 x 762 x 157]	<a href="#">PDF</a>
<a href="#">SCE-L9N308LP</a>	\$224.00	9.00 x 30.00 x 8.18 [229 x 762 x 208]	<a href="#">PDF</a>
<a href="#">SCE-L9N366LP</a>	\$215.00	9.00 x 36.00 x 6.18 [229 x 914 x 157]	<a href="#">PDF</a>
<a href="#">SCE-L9N368LP</a>	\$216.00	9.00 x 36.00 x 8.18 [229 x 914 x 208]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].