

Enviroline Junction Series

NEMA 3R, 4, 12, and 13 Wire Trough



Your Enclosure Source®



Applications

Designed to house electrical controls, instruments, and components used in an indoor or outdoor environment to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects (falling dirt); and provide a degree of protection with respect to the harmful effects on the equipment due to the ingress of water (rain, sleet, snow).

Finish

- ANSI 61 gray or RAL 7035 powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinges
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet included
- Padlocking or keylocking latches, and tamper-resistant hardware are available.

Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 12, and 13 Wire Trough

ANSI 61 Gray	RAL 7035 Gray	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-L9126ELJ	SCE-L9126ELJLG	\$204.00	9.00 x 12.00 x 6.19 [229 x 305 x 157]	PDF	SCE-9P12L	\$26.00
SCE-L9128ELJ	SCE-L9128ELJLG	\$217.00	9.00 x 12.00 x 8.19 [229 x 305 x 208]	PDF	SCE-9P12L	\$26.00
SCE-L9186ELJ	SCE-L9186ELJLG	\$206.00	9.00 x 18.00 x 6.19 [229 x 457 x 157]	PDF	SCE-9P18L	\$37.00
SCE-L9188ELJ	SCE-L9188ELJLG	\$219.00	9.00 x 18.00 x 8.19 [229 x 457 x 208]	PDF	SCE-9P18L	\$37.00
SCE-L9246ELJ	SCE-L9246ELJLG	\$212.00	9.00 x 24.00 x 6.19 [229 x 610 x 157]	PDF	SCE-9P24L	\$40.50
SCE-L9248ELJ	SCE-L9248ELJLG	\$225.00	9.00 x 24.00 x 8.19 [229 x 610 x 208]	PDF	SCE-9P24L	\$40.50
SCE-L9306ELJ	SCE-L9306ELJLG	\$214.00	9.00 x 30.00 x 6.19 [229 x 762 x 157]	PDF	SCE-9P30L	\$44.50
SCE-L9308ELJ	SCE-L9308ELJLG	\$227.00	9.00 x 30.00 x 8.19 [229 x 762 x 208]	PDF	SCE-9P30L	\$44.50
SCE-L9366ELJ	SCE-L9366ELJLG	\$218.00	9.00 x 36.00 x 6.19 [229 x 914 x 157]	PDF	SCE-9P36L	\$48.50
SCE-L9368ELJ	SCE-L9368ELJLG	\$231.00	9.00 x 36.00 x 8.19 [229 x 914 x 208]	PDF	SCE-9P36L	\$48.50

Note: Dimensions in inches [millimeters].