

# Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Wire Trough



Your Enclosure Source®



## Applications

Designed to house electrical controls, instruments, and components used in an indoor or outdoor environment to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects (falling dirt); and provide a degree of protection with respect to the harmful effects on the equipment due to the ingress of water (rain, sleet, snow).

## Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



## Construction

- 16-gauge stainless steel Type 304
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinges
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet included
- Padlocking or keylocking latches, and tamper-resistant hardware are available.

## Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Wire Trough

| Part Number                    | Price    | Size<br>HxWxD                         | Drawing<br>Link     | Optional<br>Subpanel      | Price   |
|--------------------------------|----------|---------------------------------------|---------------------|---------------------------|---------|
| <a href="#">SCE-L9126ELJSS</a> | \$717.00 | 9.00 x 12.00 x 6.18 [229 x 305 x 157] | <a href="#">PDF</a> | <a href="#">SCE-9P12L</a> | \$26.00 |
| <a href="#">SCE-L9128ELJSS</a> | \$760.00 | 9.00 x 12.00 x 8.18 [229 x 305 x 208] | <a href="#">PDF</a> | <a href="#">SCE-9P12L</a> | \$26.00 |
| <a href="#">SCE-L9186ELJSS</a> | \$797.00 | 9.00 x 18.00 x 6.18 [229 x 457 x 157] | <a href="#">PDF</a> | <a href="#">SCE-9P18L</a> | \$37.00 |
| <a href="#">SCE-L9188ELJSS</a> | \$844.00 | 9.00 x 18.00 x 8.18 [229 x 457 x 208] | <a href="#">PDF</a> | <a href="#">SCE-9P18L</a> | \$37.00 |
| <a href="#">SCE-L9246ELJSS</a> | \$803.00 | 9.00 x 24.00 x 6.18 [229 x 610 x 157] | <a href="#">PDF</a> | <a href="#">SCE-9P24L</a> | \$40.50 |
| <a href="#">SCE-L9248ELJSS</a> | \$851.00 | 9.00 x 24.00 x 8.18 [229 x 610 x 208] | <a href="#">PDF</a> | <a href="#">SCE-9P24L</a> | \$40.50 |
| <a href="#">SCE-L9306ELJSS</a> | \$871.00 | 9.00 x 30.00 x 6.18 [229 x 762 x 157] | <a href="#">PDF</a> | <a href="#">SCE-9P30L</a> | \$44.50 |
| <a href="#">SCE-L9308ELJSS</a> | \$924.00 | 9.00 x 30.00 x 8.18 [229 x 762 x 208] | <a href="#">PDF</a> | <a href="#">SCE-9P30L</a> | \$44.50 |
| <a href="#">SCE-L9366ELJSS</a> | \$936.00 | 9.00 x 36.00 x 6.18 [229 x 914 x 157] | <a href="#">PDF</a> | <a href="#">SCE-9P36L</a> | \$48.50 |
| <a href="#">SCE-L9368ELJSS</a> | \$992.00 | 9.00 x 36.00 x 8.18 [229 x 914 x 208] | <a href="#">PDF</a> | <a href="#">SCE-9P36L</a> | \$48.50 |

Note: Dimensions in inches [millimeters].