

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Wall-Mount Stainless Steel Wire Trough with Window



Your Enclosure Source®



Applications

Designed to house electrical controls, instruments, and components used in an indoor or outdoor environment to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects (falling dirt); and provide a degree of protection with respect to the harmful effects on the equipment due to the ingress of water (rain, sleet, snow).

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Construction

- 16-gauge stainless steel Type 304
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinges
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet included
- Padlocking or keylocking latches, and tamper-resistant hardware are available.

Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Wall-Mount Stainless Steel Wire Trough with Window

Part Number	Price	Size HxWxD	Drawing Link	Subpanel	Price
SCE-L9126ELJWSS	\$1,034.00	9.00 x 12.00 x 6.18 [229 x 305 x 157]	PDF	SCE-9P12L	\$26.00
SCE-L9128ELJWSS	\$1,097.00	9.00 x 12.00 x 8.18 [229 x 305 x 208]	PDF	SCE-9P12L	\$26.00
SCE-L9186ELJWSS	\$1,045.00	9.00 x 18.00 x 6.18 [229 x 457 x 157]	PDF	SCE-9P18L	\$37.00
SCE-L9188ELJWSS	\$1,107.00	9.00 x 18.00 x 8.18 [229 x 457 x 208]	PDF	SCE-9P18L	\$37.00
SCE-L9246ELJWSS	\$1,140.00	9.00 x 24.00 x 6.18 [229 x 610 x 157]	PDF	SCE-9P24L	\$40.50
SCE-L9248ELJWSS	\$1,209.00	9.00 x 24.00 x 8.18 [229 x 610 x 208]	PDF	SCE-9P24L	\$40.50
SCE-L9306ELJWSS	\$1,151.00	9.00 x 30.00 x 6.18 [229 x 762 x 157]	PDF	SCE-9P30L	\$44.50
SCE-L9308ELJWSS	\$1,220.00	9.00 x 30.00 x 8.18 [229 x 762 x 208]	PDF	SCE-9P30L	\$44.50
SCE-L9366ELJWSS	\$1,163.00	9.00 x 36.00 x 6.18 [229 x 914 x 157]	PDF	SCE-9P36L	\$48.50
SCE-L9368ELJWSS	\$1,233.00	9.00 x 36.00 x 8.18 [229 x 914 x 208]	PDF	SCE-9P36L	\$48.50

Note: Dimensions in inches [millimeters].