



# Vacuum Suction Cups with Fittings - Elastodur



Part No. [10.01.01.13244](#)  
Model No. [SPF-30-ED-65-G1/8-AG](#)



Part No. [10.01.06.03489](#)  
Model No. [SPB1-10-ED-65-M5-AG](#)



Part No. [10.01.06.03457](#)  
Model No. [SPB2-30-ED-65-G1/8-AG](#)

Schmalz Elastodur suction cups are a durable choice for most cardboard and rigid packaging vacuum applications. AutomationDirect.com's offering includes flat and bellows cups with G-thread (BSPP) fittings. Sizes range from 10 to 60mm diameter. Replacement cups are available for all sizes.

## Features:

- Elastodur cup material with aluminum fitting
- Flat, single bellows and double bellows styles
- Sizes 10mm to 60mm diameter
- Fitting sizes M5 to G 1/4

Vacuum Suction Cups with Fittings - Elastodur									
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs	
<a href="#">10.01.01.13240</a>	<a href="#">SPF-20-ED-65-G1/8-AG</a>	\$12.50	Flat	-	20mm	G1/8 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.01.13244</a>	<a href="#">SPF-30-ED-65-G1/8-AG</a>	\$14.00			30mm		<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.01.13246</a>	<a href="#">SPF-40-ED-65-G1/4-AG</a>	\$20.00			40mm	G1/4 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.01.13248</a>	<a href="#">SPF-50-ED-65-G1/4-AG</a>	\$22.00			50mm		<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03489</a>	<a href="#">SPB1-10-ED-65-M5-AG</a>	\$13.00	Bellows	1	10mm	M5 male	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03492</a>	<a href="#">SPB1-20-ED-65-G1/8-AG</a>	\$14.50			20mm	G1/8 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03496</a>	<a href="#">SPB1-30-ED-65-G1/8-AG</a>	\$17.50			30mm		<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03498</a>	<a href="#">SPB1-40-ED-65-G1/4-AG</a>	\$23.00			40mm	<a href="#">PDF</a>	<a href="#">PDF</a>		
<a href="#">10.01.06.03500</a>	<a href="#">SPB1-50-ED-65-G1/4-AG</a>	\$26.00			50mm	G1/4 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03502</a>	<a href="#">SPB1-60-ED-65-G1/4-AG</a>	\$28.00		60mm	<a href="#">PDF</a>		<a href="#">PDF</a>		
<a href="#">10.01.06.03453</a>	<a href="#">SPB2-20-ED-65-G1/8-AG</a>	\$18.00		2	1	20mm	G1/8 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.03457</a>	<a href="#">SPB2-30-ED-65-G1/8-AG</a>	\$21.50				30mm		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.03459</a>	<a href="#">SPB2-40-ED-65-G1/4-AG</a>	\$27.50			40mm	G1/4 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>	
<a href="#">10.01.06.03461</a>	<a href="#">SPB2-50-ED-65-G1/4-AG</a>	\$33.00			50mm		<a href="#">PDF</a>	<a href="#">PDF</a>	



Part No. [10.01.01.12370](#)  
Model No. [SPF-20-ED-65-SC040](#)



Part No. [10.01.06.02782](#)  
Model No. [SPB1-10-ED-65-SC030](#)



Part No. [10.01.06.03409](#)  
Model No. [SPB2-20-ED-65-SC040](#)

Replacement Vacuum Suction Cups - Elastodur							
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs	
<a href="#">10.01.01.12370</a>	<a href="#">SPF-20-ED-65-SC040</a>	\$7.75	Flat	-	20mm	<a href="#">PDF</a>	
<a href="#">10.01.01.12372</a>	<a href="#">SPF-30-ED-65-SC040</a>	\$9.25			30mm	<a href="#">PDF</a>	
<a href="#">10.01.01.12373</a>	<a href="#">SPF-40-ED-65-SC040</a>	\$12.50			40mm	<a href="#">PDF</a>	
<a href="#">10.01.01.12374</a>	<a href="#">SPF-50-ED-65-SC040</a>	\$14.50			50mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02782</a>	<a href="#">SPB1-10-ED-65-SC030</a>	\$7.75	Bellows	1	10mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02452</a>	<a href="#">SPB1-20-ED-65-SC040</a>	\$9.25			20mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02454</a>	<a href="#">SPB1-30-ED-65-SC040</a>	\$12.00			30mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02455</a>	<a href="#">SPB1-40-ED-65-SC050</a>	\$14.50			40mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02456</a>	<a href="#">SPB1-50-ED-65-SC050</a>	\$18.00			50mm	<a href="#">PDF</a>	
<a href="#">10.01.06.02457</a>	<a href="#">SPB1-60-ED-65-SC050</a>	\$20.00		60mm	<a href="#">PDF</a>		
<a href="#">10.01.06.03409</a>	<a href="#">SPB2-20-ED-65-SC040</a>	\$13.00		2	1	20mm	<a href="#">PDF</a>
<a href="#">10.01.06.03411</a>	<a href="#">SPB2-30-ED-65-SC040</a>	\$17.00				30mm	<a href="#">PDF</a>
<a href="#">10.01.06.03412</a>	<a href="#">SPB2-40-ED-65-SC050</a>	\$20.50				40mm	<a href="#">PDF</a>
<a href="#">10.01.06.03413</a>	<a href="#">SPB2-50-ED-65-SC050</a>	\$25.50				50mm	<a href="#">PDF</a>

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).