



Vacuum Suction Cups with Fittings - Silicone



Part No. [10.01.06.00092](#)
Model No. FSGA-43-SI-55-G1/4-AG



Part No. [10.01.06.03526](#)
Model No. SPB4-40-SI-55-G1/4-AG

Schmalz silicone suction cups are an excellent choice for applications requiring resistance to elevated temperatures and FDA requirements. AutomationDirect.com's offering includes bellows cups with G-thread (BSPP) fittings. Sizes range from 14 to 63mm diameter. Replacement cups are available for all sizes.

Features:

- Silicone cup material with aluminum fitting
- Single and quadruple bellows styles
- Sizes 14 to 63mm diameter
- Fitting sizes G 1/8 to G 1/4

Vacuum Suction Cups with Fittings - Silicone								
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs
10.01.06.00384	FSGA-14-SI-55-G1/8-AG	\$12.50	Bellows	1	14mm	G1/8 male BSPP	PDF	PDF
10.01.06.00393	FSGA-20-SI-55-G1/8-AG	\$13.50			20mm		PDF	PDF
10.01.06.00091	FSGA-33-SI-55-G1/4-AG	\$16.50			33mm	G1/4 male BSPP	PDF	PDF
10.01.06.00092	FSGA-43-SI-55-G1/4-AG	\$19.00			43mm		PDF	PDF
10.01.06.00093	FSGA-53-SI-55-G1/4-AG	\$23.50			53mm		PDF	PDF
10.01.06.00686	FSGA-63-SI-55-G1/4-AG	\$31.00			63mm		PDF	PDF
10.01.06.03515	SPB4-20-SI-55-G1/4-AG	\$22.00		4	20mm		PDF	PDF
10.01.06.03521	SPB4-30-SI-55-G1/4-AG	\$24.50			30mm		PDF	PDF
10.01.06.03526	SPB4-40-SI-55-G1/4-AG	\$32.00			40mm		PDF	PDF
10.01.06.03532	SPB4-50-SI-55-G1/4-AG	\$42.00			50mm		PDF	PDF



Part No. [10.01.06.00127](#)
Model No. FGA-43-SI-55-N018



Part No. [10.01.06.02590](#)
Model No. SPB4-40-SI-55-SC090

Replacement Vacuum Suction Cups - Silicone						
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs
10.01.06.00371	FGA-14-SI-55-N016	\$9.00	Bellows	1	14mm	PDF
10.01.06.00374	FGA-20-SI-55-N016	\$10.00			20mm	PDF
10.01.06.00126	FGA-33-SI-55-N018	\$10.50			33mm	PDF
10.01.06.00127	FGA-43-SI-55-N018	\$13.50			43mm	PDF
10.01.06.00128	FGA-53-SI-55-N018	\$17.50			53mm	PDF
10.01.06.00689	FGA-63-SI-55-N018	\$25.00			63mm	PDF
10.01.06.02588	SPB4-20-SI-55-SC080	\$15.50		4	20mm	PDF
10.01.06.02589	SPB4-30-SI-55-SC080	\$18.00			30mm	PDF
10.01.06.02590	SPB4-40-SI-55-SC090	\$24.00			40mm	PDF
10.01.06.02613	SPB4-50-SI-55-SC090	\$34.00			50mm	PDF

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).