

NEMA 1 Screw Cover Wall-Mount



SC080806NK



SC080806

Applications

This style is designed for use as a junction box and pull box in commercial and general industrial applications.

Construction

- Bodies and doors fabricated from 16-, 14-, or 12-gauge steel
- Flat, removable covers fastened with plated steel screws
- Cover design permits easy removal without extracting cover screws
- Mounting holes on back of enclosure
- Available with or without knockouts
- Removable concentric knockouts on all four sides of standard enclosures with knockouts

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 50, 1 [UL File E23553]
- Meets NEMA/EEMAC 1 requirements



NEMA 1 Screw Cover Wall-Mount							
Painted				Body/Door Steel Gauge	Enclosure SizeHxD	Knockout Pattern	
With Knockouts	Price	Without Knockouts	Price			Width Side	Height Side
SC040404*	\$11.25	SC040404NK*	\$11.25	16/16	4.13 x 4.13 x 4.47 [105 x 105 x 114]	A	A
SC040604*	\$13.50	SC040604NK*	\$13.50	16/16	6.13 x 4.13 x 4.47 [156 x 105 x 114]	A	A-B-A
SC060604	\$16.00	SC060604NK	\$16.00	16/16	6.13 x 6.13 x 4.47 [156 x 156 x 114]	A-B-A	A-B-A
SC060606	\$19.25	SC060606NK	\$19.25	16/16	6.13 x 6.13 x 6.47 [156 x 156 x 164]	A-B-A	A-B-A
SC060804	\$18.75	SC060804NK	\$18.75	16/16	8.13 x 6.13 x 4.47 [207 x 156 x 114]	A-B-A	A-B-A
SC060806	\$21.50	SC060806NK	\$21.50	16/16	8.13 x 6.13 x 6.47 [207 x 156 x 164]	A-B-A	A-B-A
SC061204	\$25.00	SC061204NK	\$25.00	16/16	12.13 x 6.13 x 4.47 [308 x 156 x 114]	A-B-A	B-A-F-F-A-B
SC061206	\$27.00	SC061206NK	\$27.00	16/16	12.13 x 6.13 x 6.47 [308 x 156 x 164]	A-B-A	B-A-F-F-A-B
SC080804	\$22.00	SC080804NK	\$22.00	16/16	8.13 x 8.13 x 4.47 [207 x 207 x 114]	A-B-A	A-B-A
SC080806	\$26.50	SC080806NK	\$26.50	16/16	8.13 x 8.13 x 6.47 [207 x 207 x 164]	A-B-A	A-B-A
SC080808	\$30.00	SC080808NK	\$30.00	16/16	8.00 x 8.13 x 8.13 [203 x 207 x 207]	A-B-A	A-B-A
SC081004	\$25.00	SC081004NK	\$25.00	16/16	10.13 x 8.13 x 4.47 [257 x 207 x 114]	A-B-A	B-A-F-F-A
SC081006	\$30.00	SC081006NK	\$30.00	16/16	10.13 x 8.13 x 6.47 [257 x 207 x 164]	A-B-A	B-A-F-F-A
SC081204	\$28.50	SC081204NK	\$28.50	16/16	12.13 x 8.13 x 4.47 [308 x 207 x 114]	A-B-A	B-A-F-F-A-B
SC081206	\$32.50	SC081206NK	\$32.50	16/16	12.13 x 8.13 x 6.47 [308 x 207 x 164]	A-B-A	B-A-F-F-A-B

Notes: Dimensions in inches [millimeters]
 Not UL listed.
 A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

Table continued on next page

NEMA 1 Screw Cover Wall-Mount



Table continued from previous page

NEMA 1 Screw Cover Wall-Mount							
Painted				Body/Door Steel Gauge	Enclosure SizeHxWxD	Knockout Pattern	
With Knockouts	Price	Without Knockouts	Price			Width Side	Height Side
SC101004	\$29.00	SC101004NK	\$29.00	16/16	10.13 x 10.13 x 4.47 [257 x 257 x 114]	B-A-F-F-A	B-A-F-F-A
SC101006	\$34.50	SC101006NK	\$34.50	16/16	10.13 x 10.13 x 6.47 [257 x 257 x 164]	B-A-F-F-A	B-A-F-F-A
SC101204	\$32.50	SC101204NK	\$32.50	16/16	12.13 x 10.13 x 4.47 [308 x 257 x 114]	B-A-F-F-A	B-A-F-F-A-B
SC101206	\$39.00	SC101206NK	\$39.00	16/16	12.13 x 10.13 x 6.47 [308 x 257 x 164]	B-A-F-F-A	B-A-F-F-A-B
SC121204	\$37.00	SC121204NK	\$37.00	16/16	12.13 x 12.13 x 4.47 [308 x 308 x 114]	B-A-F-F-A-B	B-A-F-F-A-B
SC121206	\$43.50	SC121206NK	\$43.50	16/16	12.13 x 12.13 x 6.47 [308 x 308 x 164]	B-A-F-F-A-B	B-A-F-F-A-B
SC121208	\$46.00	SC121208NK	\$46.00	16/16	12.00 x 12.13 x 8.13 [305 x 308 x 207]	B-A-F-F-A-B	B-A-F-F-A-B
SC121210	\$49.50	SC121210NK	\$49.50	16/16	12.00 x 12.13 x 10.13 [305 x 308 x 257]	B-A-F-F-A-B	B-A-F-F-A-B
SC121212	\$76.00	SC121212NK	\$76.00	16/16	12.00 x 12.13 x 12.13 [305 x 308 x 308]	B-A-F-F-A-B	B-A-F-F-A-B
SC121504	\$43.00	SC121504NK	\$43.00	16/16	15.13 x 12.13 x 4.47 [384 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC121506	\$50.00	SC121506NK	\$50.00	16/16	15.13 x 12.13 x 6.47 [384 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC121804	\$50.00	SC121804NK	\$50.00	16/16	18.13 x 12.13 x 4.47 [461 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC121806	\$58.00	SC121806NK	\$58.00	16/16	18.13 x 12.13 x 6.47 [461 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC122404	\$64.00	SC122404NK	\$64.00	16/16	24.12 x 12.13 x 4.47 [613 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC122406	\$74.00	SC122406NK	\$74.00	16/16	24.12 x 12.13 x 6.47 [613 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC122408	\$87.00	SC122408NK	\$87.00	16/16	24.00 x 12.13 x 8.13 [610 x 308 x 207]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC122410	\$74.00	SC122410NK	\$74.00	16/16	24.00 x 12.13 x 10.13 [610 x 308 x 257]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC122412	\$77.00	SC122412NK	\$77.00	16/16	24.00 x 12.13 x 12.13 [610 x 308 x 308]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
SC151504	\$52.00	SC151504NK	\$52.00	16/16	15.13 x 15.13 x 4.47 [384 x 384 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC151506	\$58.00	SC151506NK	\$58.00	16/16	15.13 x 15.13 x 6.47 [384 x 384 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC151804	\$64.00	SC151804NK	\$64.00	16/16	18.13 x 15.13 x 4.47 [461 x 384 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC151806	\$67.00	SC151806NK	\$67.00	16/16	18.13 x 15.13 x 6.47 [461 x 384 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC181804	\$67.00	SC181804NK	\$67.00	16/16	18.13 x 18.13 x 4.47 [461 x 461 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC181806	\$78.00	SC181806NK	\$78.00	16/16	18.13 x 18.13 x 6.47 [461 x 461 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC181808	\$87.00	SC181808NK	\$87.00	16/16	18.00 x 18.13 x 8.13 [457 x 461 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC181810	\$113.00	SC181810NK	\$113.00	16/16	18.00 x 18.13 x 10.13 [457 x 461 x 257]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC181812	\$97.00	SC181812NK	\$97.00	16/16	18.00 x 18.13 x 12.13 [457 x 461 x 308]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC182404	\$103.00	SC182404NK	\$103.00	16/16	24.12 x 18.13 x 4.47 [613 x 461 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC182406	\$122.00	SC182406NK	\$122.00	16/16	24.12 x 18.13 x 6.47 [613 x 461 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC242404	\$135.00	SC242404NK	\$135.00	14/14	24.12 x 24.13 x 4.49 [613 x 613 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A

Notes: Dimensions in inches [millimeters]
 Not UL listed.
 A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

Table continued on next page

NEMA 1 Screw Cover Wall-Mount



Table continued from previous page

NEMA 1 Screw Cover Wall-Mount							
Painted				Body/Door Steel Gauge	Enclosure SizeHxWxD	Knockout Pattern	
With Knockouts	Price	Without Knockouts	Price			Width Side	Height Side
SC242406	\$157.00	SC242406NK	\$157.00	14/14	24.12 x 24.13 x 6.49 [613 x 613 x 165]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC242408	\$174.00	SC242408NK	\$174.00	14/14	24.00 x 24.15 x 8.15 [610 x 613 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC242410	\$247.00	SC242410NK	\$247.00	14/14	24.00 x 24.15 x 10.15 [610 x 613 x 258]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
SC242412	\$268.00	SC242412NK	\$268.00	14/14	24.00 x 24.15 x 12.15 [610 x 613 x 309]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC303008NK	\$322.00	12/12	30.00 x 30.19 x 8.19 [762 x 767 x 208]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC303010NK	\$381.00	12/12	30.00 x 30.19 x 10.19 [762 x 767 x 259]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC303012NK	\$418.00	12/12	30.00 x 30.19 x 12.19 [762 x 767 x 310]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC363608NK	\$350.00	12/12	36.00 x 36.19 x 8.19 [914 x 919 x 208]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC363610NK	\$387.00	12/12	36.00 x 36.19 x 10.19 [914 x 919 x 259]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	SC363612NK	\$498.00	12/12	36.00 x 36.19 x 12.19 [914 x 919 x 310]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A

Notes: Dimensions in inches [millimeters]
Not UL listed.
A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

NEMA 1 Screw Cover Wall-Mount



Grounding Kit		
Part Number	Description	Price
WGNDKT	Grounding Kit	\$3.25
Note: Field grounding kit includes necessary parts to properly ground enclosure..		

Dimensions

