

Stride SE2 Series Managed Industrial Ethernet Switches



Stride SE2 Series Managed Models				
Part Number	Price	Ethernet Ports	Fiber Ports	Input Power (max)
<u>SE2-SW8M-2C1</u>	\$648.00	6	2 SC	8.1 W

*Optional SFP modules sold separately.

Features

- Modbus TCP management capability
- EtherNet/IP management capability
- Wide temp range
- DIN-rail mount with optional panel mount accessory
- Metal housing
- 12, 24 VDC redundant input
- Gigabit Ethernet (GbE) models
- Haz Loc
- 5-year warranty

Panel Mounting Brackets

- Stride SE2 series DIN-rail mounted switches can be panel mounted with the addition of the optional panel mounting brackets [SE2-PM1](#) or [SE2-PM3](#).

SE2-Series Panel Mounting Brackets		
Part Number	Price	For use with switch model
<u>SE2-PM1</u>	Retired	SE2-SW5Ux, SE2-SW8U-x, and SE2-MCx
<u>SE2-PM3</u>	Retired	SE2-SWPx and all SE2 managed switches

