

# Sensor Tester



## Features

- Fast field check of various sensor types
- LED and acoustic indicator
- Current supply to 100mA
- Rechargeable battery
- Adapted to universal micro-USB charger



SEN-TESTER-001				
Part Number	Price	Description	Weight	Drawing Link
<a href="#">SEN-TESTER-001</a>	\$73.00	AutomationDirect sensor tester, 24 VDC output. 9V rechargeable battery included.	96g	<a href="#">PDF</a>

Specifications	
<b>Sensor Supply Voltage</b>	24VDC
<b>Max Sensor Supply Current</b>	100mA
<b>Output Types</b>	PNP and NPN and push -pull
<b>Current Limit</b>	Yes
<b>Rechargeable Battery Type</b>	LiPo 9V (min 500mAh)
<b>Standard Battery Type</b>	Alkaline 6LR61 9V
<b>Rechargeable Battery Included</b>	LiPo 9V; 600mAh
<b>Battery Life (600 mAh)</b>	> 2 hours at 50 mA
<b>Charging Time (at 500mA)</b>	< 5 hours
<b>Automatic Switch Off</b>	After ~120 seconds of non-use
<b>LED, green</b>	Supply Voltage
<b>LED, green blinking (1Hz)</b>	Low battery (< 15% full)
<b>LED, green blinking (4Hz)</b>	Charging, phase 1 ( $\leq$ 90% full)
<b>LED, green blinking (2Hz)</b>	Charging, phase 2 ( $>$ 90% full)
<b>LED, yellow</b>	Output state
<b>Micro-USB interface for charger</b>	Yes
<b>Charger Type (not included)</b>	Universal mobile phone charger
<b>Enclosure Rating</b>	IP40

NOTE: Use only LiPo 9V (min 500mAh) or Alkaline 6LR61 9V.  
Do NOT charge Alkaline 6LR61 9V.