

Sensor Tester



Features

- Fast field check of various sensor types
- LED and acoustic indicator
- Current supply to 100mA
- Rechargeable battery
- Adapted to universal micro-USB charger



| SEN-TESTER-001 | | | | |
|---------------------------------------|---------|--|--------|----------------------------|
| Part Number | Price | Description | Weight | Drawing Link |
| <u>SEN-TESTER-001</u> | \$73.00 | AutomationDirect sensor tester, 24 VDC output. 9V rechargeable battery included. | 96g | <u>PDF</u> |

| Specifications | |
|---------------------------------|--------------------------------------|
| Sensor Supply Voltage | 24VDC |
| Max Sensor Supply Current | 100mA |
| Output Types | PNP and NPN and push -pull |
| Current Limit | Yes |
| Rechargeable Battery Type | LiPo 9V (min 500mAh) |
| Standard Battery Type | Alkaline 6LR61 9V |
| Rechargeable Battery Included | LiPo 9V; 600mAh |
| Battery Life (600 mAh) | > 2 hours at 50 mA |
| Charging Time (at 500mA) | < 5 hours |
| Automatic Switch Off | After ~120 seconds of non-use |
| LED, green | Supply Voltage |
| LED, green blinking (1Hz) | Low battery (< 15% full) |
| LED, green blinking (4Hz) | Charging, phase 1 (\leq 90% full) |
| LED, green blinking (2Hz) | Charging, phase 2 (> 90% full) |
| LED, yellow | Output state |
| Micro-USB interface for charger | Yes |
| Charger Type (not included) | Universal mobile phone charger |
| Enclosure Rating | IP40 |

NOTE: Use only LiPo 9V (min 500mAh) or Alkaline 6LR61 9V.
Do NOT charge Alkaline 6LR61 9V.