

Sensor Tester



Features

- Fast field check of various sensor types
- LED and acoustic indicator
- Current supply to 100mA
- Rechargeable battery
- Adapted to universal micro-USB charger



SEN-TESTER-001				
Part Number	Price	Description	Weight	Drawing Link
<u>SEN-TESTER-001</u>	\$73.00	AutomationDirect sensor tester, 24 VDC output. 9V rechargeable battery included.	96g	<u>PDF</u>

Specifications	
Sensor Supply Voltage	24VDC
Max Sensor Supply Current	100mA
Output Types	PNP and NPN and push -pull
Current Limit	Yes
Rechargeable Battery Type	LiPo 9V (min 500mAh)
Standard Battery Type	Alkaline 6LR61 9V
Rechargeable Battery Included	LiPo 9V; 600mAh
Battery Life (600 mAh)	> 2 hours at 50 mA
Charging Time (at 500mA)	< 5 hours
Automatic Switch Off	After ~120 seconds of non-use
LED, green	Supply Voltage
LED, green blinking (1Hz)	Low battery (< 15% full)
LED, green blinking (4Hz)	Charging, phase 1 (\leq 90% full)
LED, green blinking (2Hz)	Charging, phase 2 (> 90% full)
LED, yellow	Output state
Micro-USB interface for charger	Yes
Charger Type (not included)	Universal mobile phone charger
Enclosure Rating	IP40

NOTE: Use only LiPo 9V (min 500mAh) or Alkaline 6LR61 9V.
Do NOT charge Alkaline 6LR61 9V.