



Stripping & Crimping Tools

Overview

Southwire’s cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.

Features

- MP61**
- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
 - Crimps: insulated and non-insulated terminals/connectors
 - Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws

- S1020SOLUS**
- Strips and cuts up to 10-20 AWG solid and 12-22 AWG stranded wire
 - Double-dipped grip for comfortable fit
 - Serrated nose holds cable for easy twisting and pulling
 - Spring-loaded for self-opening action



S1020SOLUS



MP61

Cable Shears and Pliers					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
MP61	Southwire multi-purpose crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors.	9in	1	0.49	\$22.00
S1020SOLUS	Southwire multi-purpose cutting and stripping tool, beveled cutting edges, 22-10 AWG capacity.	6in	1	0.31	\$12.50