


Southwire™

TOOLS & EQUIPMENT

Stripping & Crimping Tools

Overview

Southwire's cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.

Features

MP61

- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
- Crimps: insulated and non-insulated terminals/connectors
- Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws

S1020SOLUS

- Strips and cuts up to 10-20 AWG solid and 12-22 AWG stranded wire
- Double-dipped grip for comfortable fit
- Serrated nose holds cable for easy twisting and pulling
- Spring-loaded for self-opening action


S1020SOLUS

MP61

Cable Shears and Pliers

| Part Number | Description | Tool Length | Qty/Pkg | Weight (lbs) | Price |
|--------------------------|--|-------------|---------|--------------|---------|
| <u>MP61</u> | Southwire multi-purpose crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors. | 9in | 1 | 0.49 | \$22.00 |
| <u>S1020SOLUS</u> | Southwire multi-purpose cutting and stripping tool, beveled cutting edges, 22-10 AWG capacity. | 6in | 1 | 0.31 | \$12.50 |