

Enclosure Accessories – SolarShield Series HMI Covers

**HMICVR1008**

Construction

- Patented design with non-metallic, hinged inner doors to shield screen from the sun and allow for hands-free use
- Universal covers can be used with either nonmetallic or metallic enclosures
- Fits most standard 20 x 14in and smaller HMI screens
- Lightweight, high-impact rated, UV-resistant polycarbonate material construction
- Stainless steel hardware kit included
- Padlockable for increased security
- Simple and easy installation using common tools
- Installation instructions and drill template provided
- Color: Pantone 428 C
- Temperature Range -40°F to +248°F (-40°C to +120°C)

Listings

- UL File No: E64358
- Maintains NEMA Type 4/4X enclosure rating when paired with a NEMA Type 4/4X HMI device
- Outdoor UV Exposure (UL 746C) (f1) Rated



HMI Covers				
Part Number	Price	Dimensions	Cutout Size	Drawing Link
<u>HMICVR1008</u>	\$168.00	10.38 x 13.13 x 2.50 [264 x 334 x 64]	7.25 x 9.88 [184 x 251]	PDF
<u>HMICVR1611</u>	\$287.00	14.36 x 19.10 x 2.59 [365 x 485 x 66]	11.25 x 15.88 [286 x 403]	PDF
<u>HMICVR2014</u>	\$395.00	17.33 x 23.07 x 2.59 [440 x 586 x 66]	14.25 x 19.88 [362 x 505]	PDF

Note: Dimensions in in [mm].

Enclosure Accessories – SolarShield Series Clear HMI Covers



HMICVR1008C

Construction

- Clear polycarbonate cover permits viewing of HMI while cover is closed
- Universal covers can be used with either nonmetallic or metallic enclosures
- Fits most standard 20 x 14in and smaller HMI screens
- Lightweight, high-impact rated, UV-resistant polycarbonate material construction
- Stainless steel hardware kit included
- Padlockable for increased security
- Simple and easy installation with the use of common tools
- Installation instructions and drill template provided
- Color: Pantone 428 C
- Temperature Range -40°F to +248°F (-40°C to +120°C)

Listings

- UL File No: E64358
- Maintains NEMA Type 4/4X enclosure rating when paired with a NEMA Type 4/4X HMI device
- Outdoor UV Exposure (UL 746C) (f1) Rated



HMI Covers				
Part Number	Price	Dimensions	Cutout Size	Drawing Link
<u>HMICVR1008C</u>	\$152.00	10.38 x 13.13 x 2.50 [264 x 334 x 64]	7.25 x 9.88 [184 x 251]	PDF
<u>HMICVR1611C</u>	\$259.00	14.36 x 19.10 x 2.59 [365 x 485 x 66]	11.25 x 15.88 [286 x 403]	PDF
<u>HMICVR2014C</u>	\$357.00	17.33 x 23.07 x 2.59 [440 x 586 x 66]	14.25 x 19.88 [362 x 505]	PDF

Note: Dimensions in in [mm].