

Stride[®] Managed Industrial Ethernet Switches

Industrial Hardened Full Feature Layer 2 Switch



• For detailed specifications on all models, see following pages

		SE Series	SE2 Series
Price			
		starting at \$519.00 (5 port)	starting at \$648.00 (8 port)
Full Feature Layer 2 Switch			
		✓	✓
Industrial Temperature Ranges			
Wide Temp		-40 to +75°C	-40 to +75°C
Ethernet Connectivity			
RJ45 Ports		up to 1000 Mbps	up to 1000 Mbps
Fiber Optic Ports		✓	✓
SFP Ports		✓	✓
Port Count			
		5,8,10,16	8,16,18
Industrial Protocol Management			
Modbus TCP		Read	Full Management
EtherNet/IP		—	Full Full Management
Network Redundancy			
STP/RSTP		✓	✓
Proprietary Fast Recovery		Real-Time Ring	AD-Ring/AD-RP
Mounting			
DIN Rail Mount		✓	✓
Panel Mount		Integrated	Optional accessory
Input Power			
Redundant Power Inputs		✓	✓
Reverse Polarity Protection		✓	✓
Power LED		✓	✓
Power Alarm		✓	✓
Agency Approvals			
UL508 / 61010		✓	✓
Haz Loc—Class 1 Div 2		✓	✓
ATEX Zone 2		✓	—
CE		✓	✓
Warranty			
		5 years	5 years