

# Stride<sup>®</sup> Managed Industrial Ethernet Switches

## Industrial Hardened Full Feature Layer 2 Switch



• For detailed specifications on all models, see following pages

<i>SE Series</i>		
<b>Price</b>		
starting at \$581.00 (5 port)		
<b>Full Feature Layer 2 Switch</b>		
✓		
<b>Industrial Temperature Ranges</b>		
	<b>Wide Temp</b>	-40 to +75°C
<b>Ethernet Connectivity</b>		
	<b>RJ45 Ports</b>	up to 1000 Mbps
	<b>Fiber Optic Ports</b>	✓
	<b>SFP Ports</b>	✓
<b>Port Count</b>		
5,8,10,16		
<b>Industrial Protocol Management</b>		
	<b>Modbus TCP</b>	Read
	<b>EtherNet/IP</b>	—
<b>Network Redundancy</b>		
	<b>STP/RSTP</b>	✓
	<b>Proprietary Fast Recovery</b>	Real-Time Ring
<b>Mounting</b>		
	<b>DIN Rail Mount</b>	✓
	<b>Panel Mount</b>	Integrated
<b>Input Power</b>		
	<b>Redundant Power Inputs</b>	✓
	<b>Reverse Polarity Protection</b>	✓
	<b>Power LED</b>	✓
	<b>Power Alarm</b>	✓
<b>Agency Approvals</b>		
	<b>UL508 / 61010</b>	✓
	<b>Haz Loc—Class 1 Div 2</b>	✓
	<b>ATEX Zone 2</b>	✓
	<b>CE</b>	✓
<b>Warranty</b>		
5 years		