

Stride[®] Unmanaged Industrial Ethernet Switches

Features

- Reliable connectivity
- Industrially hardened
- Simple installation

- For detailed specifications on all models, see following pages



| | SE Series | SE2 Series IP65 | SE3 Series DIN Rail | SE3 Series IP67 |
|--|----------------------|------------------------|----------------------------|------------------------|
| Price | | | | |
| | starting at \$129.00 | starting at \$354.00 | starting at \$72.00 | starting at \$279.00 |
| Broadcast Storm Protection | | | | |
| | — | — | — | — |
| Industrial Temperature Ranges | | | | |
| Standard Temp | -10 to +60°C | — | -10 to +65°C | — |
| Wide Temp | -40 to +85°C | -40 to +75°C | -40 to +75°C | -40 to +75°C |
| Port Connectivity | | | | |
| Port Count | 2 to 9 | 5 | 5 to 16 | 5 |
| RJ45 Port Speed | up to 100 Mbps | — | up to 1000 Mbps | — |
| M12 Port Speed | — | up to 100 Mbps | — | up to 100 Mbps |
| Fiber Optic Ports | ✓ | — | ✓ | — |
| PoE+ Ports | — | — | ✓ | — |
| SFP Ports | — | — | ✓ | — |
| Mounting | | | | |
| DIN Rail Mount | ✓ | — | ✓ | ✓ |
| Panel Mount | ✓ | ✓ | ✓ | ✓ |
| Input Power | | | | |
| Redundant Power Inputs | ✓ | ✓ | ✓ | ✓ |
| Reverse Polarity Protection | ✓ | ✓ | ✓ | ✓ |
| Power LED | ✓ | ✓ | ✓ | ✓ |
| Agency Approvals | | | | |
| UL508 or UL61010 | ✓ | ✓ | ✓ | ✓ |
| Haz Loc—Class 1 Div 2 | ✓ | — | ✓ | — |
| IECEX | ✓ | — | — | — |
| ATEX Zone 2 | ✓ | — | — | — |
| CE | ✓ | ✓ | ✓ | ✓ |
| EN50155 & EN50121 | — | ✓ | — | — |
| Warranty | | | | |
| | 5 years | 5 years | 5 years | 5 years |
| Activity, Link & Speed LEDs | | | | |
| | ✓ | ✓ | ✓ | ✓ |