

Stride Unmanaged Industrial Ethernet Switches

Features

- Reliable connectivity
 - Industrially hardened
 - Simple installation
- For detailed specifications on all models, see following pages



		SE Series	SE2 Series IP65	SE3 Series DIN Rail	SE3 Series IP67
Price					
		starting at \$129.00	starting at \$354.00	starting at \$72.00	starting at \$279.00
Broadcast Storm Protection					
		—	—	—	—
Industrial Temperature Ranges					
	Standard Temp	-10 to +60°C	—	-10 to +65°C	—
	Wide Temp	-40 to +85°C	-40 to +75°C	-40 to +75°C	-40 to +75°C
Port Connectivity					
	Port Count	2 to 9	5	5 to 16	5
	RJ45 Port Speed	up to 100 Mbps	—	up to 1000 Mbps	—
	M12 Port Speed	—	up to 100 Mbps	—	up to 100 Mbps
	Fiber Optic Ports	✓	—	✓	—
	PoE+ Ports	—	—	✓	—
	SFP Ports	—	—	✓	—
Mounting					
	DIN Rail Mount	✓	—	✓	✓
	Panel Mount	✓	✓	✓	✓
Input Power					
	Redundant Power Inputs	✓	✓	✓	✓
	Reverse Polarity Protection	✓	✓	✓	✓
	Power LED	✓	✓	✓	✓
Agency Approvals					
	UL508 or UL61010	✓	✓	✓	✓
	Haz Loc—Class 1 Div 2	✓	—	✓	—
	IECEX	✓	—	—	—
	ATEX Zone 2	✓	—	—	—
	CE	✓	✓	✓	✓
	EN50155 & EN50121	—	✓	—	—
Warranty					
		5 years	5 years	5 years	5 years
Activity, Link & Speed LEDs					
		✓	✓	✓	✓