

# Stride Unmanaged Industrial Ethernet Switches

## Features

- Reliable connectivity
  - Industrially hardened
  - Simple installation
- 
- For detailed specifications on all models, see following pages



		SE Series	SE2 Series IP65	SE3 Series DIN Rail	SE3 Series IP67
<b>Price</b>					
		starting at \$162.00	starting at \$354.00	starting at \$72.00	starting at \$279.00
<b>Broadcast Storm Protection</b>					
		—	—	—	—
<b>Industrial Temperature Ranges</b>					
	<b>Standard Temp</b>	-10 to +60°C	—	-10 to +65°C	—
	<b>Wide Temp</b>	-40 to +85°C	-40 to +75°C	-40 to +75°C	-40 to +75°C
<b>Port Connectivity</b>					
	<b>Port Count</b>	2 to 9	5	5 to 16	5
	<b>RJ45 Port Speed</b>	up to 100 Mbps	—	up to 1000 Mbps	—
	<b>M12 Port Speed</b>	—	up to 100 Mbps	—	up to 100 Mbps
	<b>Fiber Optic Ports</b>	✓	—	✓	—
	<b>PoE+ Ports</b>	—	—	✓	—
	<b>SFP Ports</b>	—	—	✓	—
<b>Mounting</b>					
	<b>DIN Rail Mount</b>	✓	—	✓	✓
	<b>Panel Mount</b>	✓	✓	✓	✓
<b>Input Power</b>					
	<b>Redundant Power Inputs</b>	✓	✓	✓	✓
	<b>Reverse Polarity Protection</b>	✓	✓	✓	✓
	<b>Power LED</b>	✓	✓	✓	✓
<b>Agency Approvals</b>					
	<b>UL508 or UL61010</b>	✓	✓	✓	✓
	<b>Haz Loc—Class 1 Div 2</b>	✓	—	✓	—
	<b>IECEX</b>	✓	—	—	—
	<b>ATEX Zone 2</b>	✓	—	—	—
	<b>CE</b>	✓	✓	✓	✓
	<b>EN50155 &amp; EN50121</b>	—	✓	—	—
<b>Warranty</b>					
		5 years	5 years	5 years	5 years
<b>Activity, Link &amp; Speed LEDs</b>					
		✓	✓	✓	✓