

# WCT Series NEMA 1 and 3R Screw-Cover Wall-Mount



## Applications

Designed for use as transformer housing, junction boxes, and service boxes.

## Finish

- ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces

## Construction

- Drip shield top and smooth seamless sides and front
- A slip-on removable cover is securely fastened with plated screws located along bottom edge
- No gasket required
- Mounting holes on back of cabinet
- Door handles provided
- Hasp for padlocking and provisions for meter seal are provided
- To remove cover, move down, then out

## Listings

- UL 50, Types 1 and 3R [UL file E23553]
- NEMA/EEMAC 1 and 3R



WCT Series NEMA 1 and 3R Screw-Cover Wall-Mount			
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
<b>WCT303012</b>	\$408.00	12/12	30.09 x 30.50 x 12.47 [764 x 775 x 317]
<b>WCT363012</b>	\$549.00		36.09 x 30.50 x 12.47 [917 x 775 x 317]
<b>WCT363612</b>	\$600.00		36.09 x 36.50 x 12.47 [917 x 927 x 317]
<b>WCT483616</b>	\$966.00		48.09 x 36.50 x 16.47 [1221 x 927 x 418]

Notes: Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawings.

## Dimensions

