

Wera Ratchets

BE A TOOL REBEL



Zyklop Metal Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets and Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price
05004004055	Wera Zyklop Metal ratchet, switch lever, 1/4in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$49.00
05004034055	Wera Zyklop Metal ratchet, switch lever, 3/8in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$56.00
05004064055	Wera Zyklop Metal ratchet, switch lever, 1/2in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$63.00



Switch Lever

Switch lever for convenient change of direction.

Wera Ratchet and Socket Sets

Zyklop Metal 3/8 in Drive Ratchet and Socket Sets



Zyklop Metal 3/8in Drive Ratchet and Socket Sets					
05004051055		05004048055			
Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, Pozidriv, internal hex, Torx and external hex, 29 pieces, 1in bit length, 3/8in drive, imperial.		\$147.00	Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, Pozidriv, internal hex, Torx and external hex, 29 pieces, 1in bit length, 3/8in drive, metric.		
		\$147.00			
Type	Size	Type	Size		
Zyklop metal ratchet	3/8in	Zyklop metal ratchet	3/8in		
Extension	3/8in x 200mm	Extension	3/8in x 200mm		
Wobble extension	3/8in x 76mm	Wobble extension	3/8in x 76mm		
Bit adaptor	3/8in x 1/4in x 44mm	Bit adaptor	3/8in x 1/4in x 44mm		
	6-point socket	(29mm)1/4, 5/16, 3/8, 7/16, 1/2, 9/16in, (30mm) 5/8, 11/16, 3/4in		6-point socket	(29mm) 8, 10, 12, 13, 15mm, (30mm) 16, 17, 18, 19mm
	External hex bit, 25mm long	5/32, 3/16, 7/32, 1/4, 5/16in		External hex bit, 25mm long	3, 4, 5, 6, 8mm
	Phillips bit 25mm long	#1, #2, #3		Phillips bit 25mm long	#1, #2, #3
	Posidriv bit 25mm long	#1, #2		Posidriv bit 25mm long	#1, #2
	Torx bit 25mm long	T15, T20, T25 T27, T30, T40		Torx bit, 25mm long	T15, T20, T25, T27, T30, T40

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.