


Wera Bit Drivers, Bits, & Adapters

Universal Bit Holder

The Rapidaptor universal bit holder is designed for bits with 1/4 in external hexagon drives. The Rapidaptor allows for mounting the bits without using the sleeve. The bit is removed by simply pushing it forward—for lightning-fast bit changes with just one hand.

Features

- Rapidaptor technology for rapid bit change
- Free-floating magnetic sleeve
- One-hand operation



Driver Bit Adapter				
Part Number	Drive Size	Overall Length	Description	Price
<u>TW-DB-ADT-MAG</u>	1/4in	2.25in (57mm)	Wera Rapidaptor magnetic driver bit adapter, 1/4in drive, 2.25in (57mm) overall length. Rapidaptor technology for rapid bit change.	\$20.00

Note: Bit-holders are warranted against manufacturer defect only.




Wera Bit Drivers, Bits, & Adapters


Driver Bit, Bitholding Screwdriver, and L-key Set

This 52-piece set packs maximum screwdriving utility into a compact, lightweight set protected by an extremely robust folding textile box.

- BiTorsion bits for long service life
- Impaktor bits for extreme conditions
- Chrome-plated Hex-Plus L-keys with ball-end hex on long arm
- One Rapidaptor bit holder for quick, one-handed bit changes
- One Kraftform Kompact bitholding screwdriver for that ergonomic Kraftform feel



Take-it-Easy Tool Finder



BiTorsion Bits



Impaktor Impact Bits

Screwdriver Bit Sets

Part Number	Part Image	Number of Pieces	Type	Size (Tip Size x Length)	Quantity Included	Set Includes	Price
05057460055		52	Phillips	#1 x 25mm	2	bitholding screwdriver with Rapidaptor quick-release chuck, Rapidaptor universal bit holder, (8) BiTorsion Phillips bits ((2) #1, (4) #2, (2) #3), (3) Impaktor Phillips bits ((2) #2, #3), (8) BiTorsion Pozidriv bits ((2) #1, (4) #2, (2) #3), (3) Impaktor Pozidriv bits ((2) #2, #3), (12) BiTorsion Torx bits ((2) T10, (2) T15, (3) T20, (2) T25, (2) T30, T40), (3) Impaktor Torx bits (T25, T30, T40), (2) BiTorsion 5.5mm flat/slotted bits, (3) Impaktor hex bits (4, 5, 6mm), (8) L-keys with Hex-Plus profile (1.5, 2, 2.5, 3, 4, 5, 6, 8mm), durable cloth pouch	\$122.00
				#2 x 25mm	4		
				#3 x 25mm	2		
			Impact-rated Phillips	#2 x 50mm	2		
				#3 x 50mm	1		
			Slotted	0.8 x 5.5mm x 25mm	1		
				1 x 5.5mm x 25mm	1		
			Pozidriv	#1 x 25mm	2		
				#2 x 25mm	4		
				#3 x 25mm	2		
			Impact-rated Pozidriv	#2 x 50mm	2		
				#3 x 50mm	1		
			Torx	T10 x 25mm	2		
				T15 x 25mm	2		
				T20 x 25mm	3		
				T25 x 25mm	2		
				T30 x 25mm	2		
				T40 x 25mm	1		
			Impact-rated Torx	T25 x 50mm	1		
				T30 x 50mm	1		
				T40 x 50mm	1		
			Impact-rated Hex Plus	4 x 50mm	1		
				5 x 50mm	1		
				6 x 50mm	1		
			Hex Plus L-key	1.5 x 50mm	1		
				2 x 56mm	1		
				2.5 x 63mm	1		
				3 x 71mm	1		
				4 x 80mm	1		
				5 x 90mm	1		
				6 x 100mm	1		
				8 x 112mm	1		

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.








Wera Bit Drivers, Bits, & Adapters

Standard Driver Bits

Wera bits are designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use, and are extremely durable.



Standard Driver Bits								
Part Number	Part Image	Type	Tip Size	Bit Length	Drive Size	Description	Package Quantity	Price
<u>TW-DB-PH-1</u>		 Phillips	#1	2.75in	1/4in	Wera #1 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.	10	\$10.00
<u>TW-DB-PH-2</u>			#2			Wera #2 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.		\$10.00
<u>TW-DB-SL-1</u>		 Slotted	3.0mm	2in		Wera 3.0mm slotted general purpose driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 10.		\$31.00

Note: Screwdriver bits are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters



Tool-Check Socket and Driver Bit Sets			Bit-Check Socket and Driver Bit Sets		
05073220055			TW-DB-SET-28R		
<p>Wera Tool-Check standard driver bit and socket set, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.</p>			\$102.00	<p>Wera Bit-Check standard driver bit set, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.</p>	
Type		Bit Size	Type		Bit Size
Zyklop Mini bit ratchet		1/4in	Zyklop Mini bit ratchet		1/4in
Rapidaptor bit holder		1/4 x 50	Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4 x 25	Socket adaptor		1/4 x 25
	Slotted bit 25mm long	1.0 x 5.5mm		Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Phillips bit, 25mm long	(2) P#, (3) #2, #3		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Slotted bit 25mm long	1.0 x 5.5mm
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	Pozidriv bit 25mm long	#1, (3) #2, #3		Square bit 25mm long	#1, (3) #2, #3
	6-point socket	5.5, 6.0, 7.0, 8.0 10.0, 12.0, 13.0mm			

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters



Tool-Check PLUS Socket and Driver Bit Sets			Tool-Check Socket and Driver Bit Sets		
05056490001			05056491001		
Wera Tool-Check PLUS standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.			\$108.00	Wera Tool-Check standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex, 39 pieces, 1in bit length, 1/4in drive, imperial.	
Type	Size		Type	Size	
Bitholding screwdriver	1/4in x 78mm		Bitholding screwdriver	1/4in x 78mm	
Zyklop mini bit ratchet	1/4in		Zyklop mini bit ratchet	1/4in	
Rapidaptor bit holder	1/4in x 50mm		Rapidaptor bit holder	1/4in x 50mm	
Socket adaptor	1/4in x 25mm		Socket adaptor	1/4in x 25mm	
	Phillips bit, 25mm long	(2) #1, (3) #2, #3		Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Pozidriv bit, 25mm long	#1, (3) #2, #3		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30		Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
	Slotted bit 25mm long	1.0 x 5.5mm		Slotted bit 25mm long	1.0 x 5.5mm
	Hex-Plus bit 25mm long	3.0, 4.0, 5.0, 6.0, 8.0mm		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm		6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.