








Wera Screwdrivers

Insulated Screwdrivers

As with all other Wera tools, safety is a top priority for series 100 VDE screwdrivers. All Wera insulated screwdrivers are individually tested at 10,000V, in accordance with IEC 60900, ensuring safe working up to 1,000V. The quality of the blades exceeds current standards with respect to hardness and torque strength.







Insulated Screwdrivers										
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Reduced Shank	Handle Length	Handle Type	Price
05006440055*		● Slotted	3.5mm	7.1in (180mm)	3.9in (100mm)	0.14in (3.5mm)	Yes	3.2in (81mm)	Kraftform ergonomic handle	\$10.00
05006441055*			4.0mm	7.8in (198mm)		0.20in (5.1mm)		\$10.50		
05006442055*			5.5mm	8.8in (223mm)	4.9in (125mm)	0.24in (6.1mm)		\$11.50		
TW-SD-VSL-1			2.5mm	8.7in (220mm)	3.1in (80mm)	0.20in (5.1mm)	No	3.2in (81mm)		\$5.50
TW-SD-VSL-2			3.0mm	9.4in (240mm)	3.9in (100mm)	0.12in (3.0mm)				\$5.75
TW-SD-VSL-3			4.0mm	10.0in (255mm)		0.24in (6.1mm)		\$7.50		
TW-SD-VSL-4			5.5mm	11.0in (280mm)	4.9in (125mm)	0.22in (5.6mm)		3.9in (99mm)		\$9.00


*Does not have a Lasertip laser-etched non-slip tip.

Wera Screwdrivers

Insulated Screwdrivers - Cont'd

Insulated Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Reduced Shank	Handle Length	Handle Type	Price
<u>05006450055*</u>		⊕ Phillips	#1	7.0in (177mm)	3.1in (80mm)	0.16in (4.0mm)	Yes	3.9in (99mm)	Kraftform ergonomic handle	\$10.50
<u>05006451055*</u>			#2	8.1in (205mm)	3.9in (100mm)	0.24in (6.1mm)		4.1in (104mm)		\$13.50
<u>TW-SD-VPH-1*</u>			#1	9.3in (236mm)	3.1in (80mm)	0.16in (4.0mm)	No	3.2in (81mm)		\$8.25
<u>TW-SD-VPH-2</u>			#2	8.1in (205mm)	3.9in (100mm)	0.24in (6.1mm)		4.1in (104mm)		\$11.00

*Does not have a Lasertip laser-etched non-slip tip.

Insulated Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>TW-SD-SET-2</u>	6		⊕ Phillips	#1 #2	(4) insulated slotted screwdrivers (2.5, 3.5, 4, 5.5mm), (2) insulated Phillips screwdrivers (#1, #2), wall mount rack	\$41.50
			⊖ Slotted	2.5mm 3.5mm 4.0mm 5.5mm		