

Wera Screwdrivers

Precision Screwdrivers

Wera Kraftform Micro precision screwdrivers feature a hand support on the easy-turning cap and a fast-turning zone below the cap to accelerate the screw driving process. This makes time-consuming grip adjustments, which are required with conventional precision screwdrivers, unnecessary.



Precision Screwdrivers								
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Handle Length	Handle Type	Price
<u>TW-SD-MSL-1</u>		 Slotted	2.0mm	6.2in (157mm)	2.4in (60mm)	3.8in (97mm)	Kraftform ergonomic handle with rotating cap	\$4.00
<u>TW-SD-MSL-2</u>			2.5mm	7.0in (177mm)	3.1in (80mm)			\$4.00
<u>TW-SD-MSL-3</u>			3.0mm					\$4.00
<u>TW-SD-MPH-1</u>		 Phillips	#0	6.2in (157mm)	2.4in (60mm)			\$4.00
<u>05118064001</u>		 External	1.3mm	5.4in (137mm)	1.6in (40mm)			\$4.00
<u>05118066001</u>			1.5mm	6.2in (157mm)	2.4in (60mm)			\$4.00
<u>05118068001</u>			2.0mm					\$3.00



Wera Screwdrivers

Precision Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>TW-SD-SET-3</u>	6		 Phillips	#00 #0	(4) precision slotted screwdrivers (1.8, 2, 2.5, 3mm), (2) precision Phillips screwdrivers (#00, #0), wall mount rack	\$29.00
			 Slotted	1.8mm 2.0mm 2.5mm 3.0mm		
<u>05073675001</u>	12		 Phillips	#00 #0	(12) Kraftform Micro precision screwdrivers (Phillips: #00, #0, torx: T5, T6, slotted: 1.5mm, 1.8mm, 2mm, 2.5mm, 3mm, hex: 0.9mm, 1.5mm, 2mm), (1) hook and loop fastener strip for storage	\$50.00
			 Torx	T5 T6		
			 Slotted	1.5mm 1.8mm 2.0mm 2.5mm 3mm		
			 Hex	0.9mm 1.5mm 2.0mm		
<u>05134000001</u>	25		 Phillips	#000 #00 #0	(25) Kraftform Micro precision screwdrivers (Phillips: #000, #00, #0, torx: T5, T6, torx w/ holding function: T5, T6, T7, T8, T10, torx plus: IP1, slotted: 1.5mm, 1.8mm, 2mm, (2) 2.5mm, 3mm, hex: 0.9mm, 1.3mm, 1.5mm, 2mm, nutdriver: 4mm, 5.5mm, (1) Microstix, (1) Lifting fork for chip removal), (1) hook and loop fastener strip for storage	\$160.00
			 Slotted	1.5mm 1.8mm 2.0mm 2.5mm 3.0mm		
			 Torx	T5 T6		
			 Torx Plus IPR	IPR1		
			 External Hex	0.9mm 1.3mm 1.5mm 2.0mm		
			 Internal Hex	4.0mm 5.5mm		
			 Microstix	(1)		
			 Spanner	(1)		