




# Wera Ratchets & Sockets

BE A TOOL REBEL


## Zyklop Mini Bit Ratchet

The Wera Zyklop mini bit ratchet is designed for easy, flexible fastening using 1/4 in bits and sockets. Its compact design features a small 6° return angle, a thumbwheel for quick operation and a switch lever for convenient direction change. It's constructed of chrome vanadium steel with a brushed chrome-plated finish for corrosion protection.



### Zyklop Mini Bit Ratchet

Part Number	Description	Price
<b>05073230055</b>	Wera Zyklop bit ratchet, switch lever, 1/4in drive, 5 degrees return angle, all-metal construction, ballpoint socket and retaining ring bit holder locking mechanism. Adapter for 1/4in sockets included.	\$36.00





# Wera Bit Drivers, Bits, & Adapters



Tool-Check Socket and Driver Bit Sets			Bit-Check Socket and Driver Bit Sets		
<b>05073220055</b>			<b>TW-DB-SET-28R</b>		
Wera Tool-Check standard driver bit and socket set, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.			\$102.00	Wera Bit-Check standard driver bit set, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.	
<b>Type</b>		<b>Bit Size</b>	<b>Type</b>		<b>Bit Size</b>
Zyklop Mini bit ratchet		1/4in	Zyklop Mini bit ratchet		1/4in
Rapidaptor bit holder		1/4 x 50	Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4 x 25	Socket adaptor		1/4 x 25
	Slotted bit 25mm long	1.0 x 5.5mm		Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Phillips bit, 25mm long	(2) P#, (3) #2, #3		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Slotted bit 25mm long	1.0 x 5.5mm
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	Pozidriv bit 25mm long	#1, (3) #2, #3		Square bit 25mm long	#1, (3) #2, #3
	6-point socket	5.5, 6.0, 7.0, 8.0 10.0, 12.0, 13.0mm			

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



# Wera Bit Drivers, Bits, & Adapters



Tool-Check PLUS Socket and Driver Bit Sets			Tool-Check Socket and Driver Bit Sets		
<b>05056490001</b>			<b>05056491001</b>		
Wera Tool-Check PLUS standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.			\$108.00	Wera Tool-Check standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex, 39 pieces, 1in bit length, 1/4in drive, imperial.	
Type	Size		Type	Size	
Bitholding screwdriver	1/4in x 78mm		Bitholding screwdriver	1/4in x 78mm	
Zyklop mini bit ratchet	1/4in		Zyklop mini bit ratchet	1/4in	
Rapidaptor bit holder	1/4in x 50mm		Rapidaptor bit holder	1/4in x 50mm	
Socket adaptor	1/4in x 25mm		Socket adaptor	1/4in x 25mm	
	Phillips bit, 25mm long	(2) #1, (3) #2, #3		Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Pozidriv bit, 25mm long	#1, (3) #2, #3		Pozidriv bit, 25mm long	#1, (3) #2, #3
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30		Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
	Slotted bit 25mm long	1.0 x 5.5mm		Slotted bit 25mm long	1.0 x 5.5mm
	Hex-Plus bit 25mm long	3.0, 4.0, 5.0, 6.0, 8.0mm		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm		6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.