

# Wera Screwdrivers

## Non-ratcheting Multi-Bit Screwdrivers

MultiWera's bitholding screwdriver with Rapidaptor quick-release chuck allows for lightning fast bit changes without any extra tools. The Kraftform Plus handle allows for comfortable ergonomic screwdriving, preventing blisters and calluses. Suitable for bits with 1/4 in external hexagon drive.



Hex Plus



Tri-Wing® Screwdriving System

Non-Ratcheting Multi-Bit Screwdrivers								
Part Number	Number of Pieces	Part Image	Type	Bit Size	Overall Length	Handle Type	Set Includes	Price
<a href="#">05059295001</a>	17		⊕ Phillips	#1, #2, #3	4.6in (117mm)	Kraftform ergonomic handle	(1) Kraftform Kompakt Rapidaptor bit holding screwdriver, (16) 3.5in standard bits (Phillips: #1, #2, #3 Pozidriv: #1, #2, #3, tamperproof torx: T10, T15, T20, T25, T30, hex: 3mm, 4mm, 5mm, 6mm, slotted: 5.5mm), (1) robust textile pouch, (1) hook and loop fastener strip for storage	\$68.00
			⊖ Slotted	5.5mm				
			⊕ External Hex	3mm, 4mm, 5mm, 6mm				
			⊕ Tamperproof Torx	T10, T15, T20, T25, T30				
			⊕ Pozidriv	#1, #2, #3				
<a href="#">05059297001</a>	33		⊕ Phillips	#1, #2, #3	4.6in (117mm)	Kraftform ergonomic handle	(1) Kraftform Kompakt Rapidaptor bit holding screwdriver, (32) 3.5in standard bits (Phillips: #1, #2, #3 Pozidriv: #1, #2, #3, tamperproof torx: T8, T10, T15, T20, T25, T27, T30, T40, tamper-proof hex: 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, Torq-set #6, #8, #10, Tri-wing #1, #2, #3, #4, slotted: 6.5mm, spanner: #4, #6, #8, #10), (1) robust textile pouch, (1) hook and loop fastener strip for storage	\$104.00
			⊖ Slotted	6.5mm				
			⊕ Tamperproof Hex	2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm				
			⊕ Tamperproof Torx	T8, T10, T15, T20, T25, T27, T30, T40				
			⊕ Pozidriv	#1, #2, #3				
			⊕ Tri-wing	#1, #2, #3, #4				
			⊕ Torq-set	#6, #8, #10				
			⊕ Spanner	#4, #6, #8, #10				

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.