













Wera Screwdrivers

Standard Screwdrivers

Wera Kraftform Plus standard screwdrivers transfer more torque with less effort, relieving physical stress even during intensive use. Combined with other practical and technical product advantages, such as the lasertip for a secure fit in the screw, and greater cam-out protection, Kraftform screwdrivers are the perfect choice for manual work.







| Standard Screwdrivers | | | | | | | | | |
|-------------------------------------|---|--|----------|-------------------|-------------------|-------------------|------------------|----------------------------|---------|
| Part Number | Part Image | Type | Tip Size | Overall Length | Shaft Length | Shaft Diameter | Handle Length | Handle Type | Price |
| <u>TW-SD-SL-1</u> |  |  Slotted | 3.0mm | 6.3in (160mm) | 3.1in (80mm) | 0.12in (3.0mm) | 3.2in (81mm) | Kraftform ergonomic handle | \$5.75 |
| <u>TW-SD-SL-2</u> |  | | 4.0mm | 7.8in (198mm) | 3.9in (100mm) | 0.16in (4.0mm) | 3.9in (99mm) | | \$4.50 |
| <u>TW-SD-SL-3</u> |  | | 5.5mm | 8.8in (223mm) | 4.9in (125mm) | 0.22in (5.6mm) | | | \$7.50 |
| <u>TW-SD-SL-4</u> |  | | 6.5mm | 12.4in (315mm) | 5.9in (150mm) | 0.26in (6.5mm) | 4.1in (104mm) | | \$10.50 |
| <u>05008027055*</u> |  | | 4.0mm | 10.0in (255mm) | 11.8in (300mm) | 0.16in (4.0mm) | 3.9in (99mm) | | \$9.00 |
| <u>05008060055*</u> |  | | 5.5mm | 11.0in (280mm) | 11.8in (300mm) | 0.24in (6.1mm) | | | \$10.00 |
| <u>TW-SD-PH-1</u> |  |  Phillips | #1 | 9.4in (240mm) | 3.1in (80mm) | 0.12in (3.0mm) | 4.1in (104mm) | | \$6.75 |
| <u>TW-SD-PH-2</u> |  | | #2 | 10.6in (269mm) | 3.9in (100mm) | 0.20in (5.1mm) | \$9.50 | | |
| <u>TW-SD-PH-3*</u> |  | | #0 | 5.6in (141mm) | 2.4in (60mm) | 0.12in (3.0mm) | 3.2in (81mm) | | \$5.25 |
| <u>05008730055</u> |  | | #2 | 15.9in (405mm) | 11.8in (300mm) | 0.24in (6.1mm) | 4.1in (104mm) | | \$11.00 |


*Includes a hardened Black Point tip instead of laser-etched non-slip tip.



Standard Screwdrivers Cont'd

| Standard Screwdrivers - Cont'd | | | | | | | | | |
|-------------------------------------|---|------------------|----------|------------------|------------------|-------------------|-------------------|----------------------------|-----------------|
| Part Number | Part Image | Type | Tip Size | Overall Length | Shaft Length | Shaft Diameter | Handle Length | Handle Type | Price |
| <u>05023105001</u> |  | External hex | 2.0mm | 5.7in (145mm) | 3.0in (75mm) | 0.12in (3.0mm) | 2.8in (70mm) | Kraftform ergonomic handle | \$3.50 |
| <u>05023107001</u> |  | | 2.5mm | 6.1in (156mm) | | | 0.16in (4.0mm) | | 3.2in (81mm) |
| <u>05023110001</u> |  | | 3.0mm | | | \$4.00 | | | |
| <u>05138262055*</u> |  | Tamperproof torx | TX20 | 7.8in (198mm) | 3.9in (100mm) | 0.18in (4.6mm) | 3.9in (99mm) | | \$8.25 |

*Includes a hardened Black Point tip instead of laser-etched non-slip tip.

| Standard Screwdriver Sets | | | | | | |
|------------------------------------|------------------|---|-------------------------|--|--|---------|
| Part Number | Number of Pieces | Part Image | Type | Tip Size | Set Includes | Price |
| <u>TW-SD-SET-1</u> | 6 |  | + Phillips - Slotted | #1 #2 3.0mm 4.0mm 5.5mm 6.5mm | (4) slotted screwdrivers (3, 4, 5.5, 6.5mm), (2) Phillips screwdrivers (#1, #2), wall mount rack | \$36.00 |