



Wera Wrenches

Metric Ratcheting Combination Wrenches

Joker metric combination ratchet wrenches revolutionize the humble wrench. The 12-point open end features a unique 6-point stop plate that enables easier turning of bolts and also provides improved grip for loosening stubborn bolts. The fine tooth ratchet mechanism is exceptional for working in tight spaces. Joker wrenches feature chrome molybdenum steel construction with a nickel-chrome coating for corrosion protection.



Metric Ratcheting Combination Wrenches						
Part Number	Wrench Type	Fastening Size	Jaw Thickness	Overall Length	Wrench Features	Price
05073268055	Combination	8mm	0.22in (5.5mm)	9.3in (235mm)	Special nut holding feature Fine tooth ratchet	\$21.00
05073270055		10mm		6.7in (171mm)		\$22.00
05073271055		11mm	0.25in (6.3mm)	6.3in (159mm)		\$23.00
05073272055		12mm	0.26in (6.6mm)	7.4in (188mm)		\$24.00
05073273055		13mm	0.28in (7.0mm)	6.5in (165mm)		\$24.00
05073274055		14mm	0.30in (7.7mm)	9.7in (246mm)		\$25.00
05073275055		15mm	0.31in (7.8mm)	8.3in (212mm)		\$27.00
05073276055		16mm	0.32in (8.2mm)	7.0in (177mm)		\$28.00
05073277055		17mm	0.33in (8.5mm)	6.5in (165mm)		\$31.00
05073278055		18mm	0.35in (9.0mm)	6.3in (159mm)		\$32.00
05073279055		19mm	0.37in (9.5mm)	7.4in (188mm)		\$35.00

Metric Ratcheting Combination Wrench Sets				
Part Number	Number of Pieces	Part Image	Set Includes	Price
05073290055	4		(4) ratcheting combination wrenches (10, 13, 17 and 19mm), durable cloth pouch	\$107.00
05020013055	11		(8) ratcheting combination wrenches (8, 10, 11, 12, 13, 14, 15, 16, 17, 18 and 19mm), durable cloth pouch	\$287.00

Wera Wrenches





Imperial Ratcheting Combination Wrenches

Joker imperial combination ratchet wrenches revolutionize the humble wrench. The 12-point open end features a unique 6-point stop plate that enables easier turning of bolts and also provides improved grip for loosening stubborn bolts. The fine tooth ratchet mechanism is exceptional for working in tight spaces. Joker wrenches feature chrome molybdenum steel construction with a nickel-chrome coating for corrosion protection.



Imperial Ratcheting Combination Wrenches						
Part Number	Wrench Type	Fastening Size	Jaw Thickness	Overall Length	Wrench Features	Price
05073280055	Combination	5/16in	0.22in (5.5mm)	5.7in (144mm)	Special nut holding feature Fine tooth ratchet	\$21.00
05073281055		3/8in		7.9in (200mm)		\$22.00
05073282055		7/16in	0.25in (6.3mm)	5.7in (144mm)		\$24.00
05073283055		1/2in	0.28in (7.0mm)	4.7in (119mm)		\$24.00
05073284055		9/16in	0.30in (7.7mm)	9.3in (235mm)		\$25.00
05073285055		5/8in	0.32in (8.2mm)	7.0in (177mm)		\$28.00
05073286055		11/16in	0.35in (9.0mm)	9.7in (246mm)		\$32.00
05073287055		3/4in	0.37in (9.5mm)	8.3in (212mm)		\$35.00

Imperial Ratcheting Combination Wrench Sets				
Part Number	Number of Pieces	Part Image	Set Includes	Price
05073295055	4		(4) ratcheting combination wrenches (7/16, 1/2, 9/16 and 3/4in), durable cloth pouch	\$107.00
05020012055	8		(8) ratcheting combination wrenches (5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16 and 3/4in), durable cloth pouch	\$205.00