



Signal Devices

Visual 57/58mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon model
- Base mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included on incandescent models
- 2-year warranty



Visual 57/58mm Base Mount Beacons 200, 201 and 202 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals	
35.5 mm Base Mount														
20010000	\$18.00	Red	PDF	Incandescent Permanent Light 57mm	12–240 V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	–		up to 5,000h		50 [1.76]			
20020000	\$18.00	Green	PDF											
20030000	\$18.00	Yellow	PDF											
20040000	\$18.00	Clear	PDF											
20050000	\$18.00	Blue	PDF	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5 A	–4 to 122°F [–20 to 50°C] IP65	up to 100,000h	Polycarbonate cap Polyamide base	66 [2.33]	Up to 2.5 mm² Screwless CAGE CLAMP® - technology (8–14 AWG)	cULus file E164155, CE, RoHS	
20110067	\$78.00	Red	PDF											
20120067	\$78.00	Green	PDF											
20130067	\$78.00	Yellow	PDF											
20140067	\$109.00	Clear	PDF											
20150067	\$119.00	Blue	PDF		24V AC/DC	< 45mA	4,000,000 flashes							82 [2.89]
20110075	\$62.00	Red	PDF											
20120075	\$62.00	Green	PDF											
20130075	\$62.00	Yellow	PDF											
20140075	\$123.00	Clear	PDF											
20150075	\$123.00	Blue	PDF	Xenon Flashing Light (0.75 Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100mA			–					
20210055	\$100.00	Red	PDF											
20220055	\$106.00	Green	PDF											
20230055	\$100.00	Yellow	PDF											
20240055	\$106.00	Clear	PDF											
20250055	\$106.00	Blue	PDF		115VAC	< 20mA								
20210067	\$100.00	Red	PDF											
20220067	\$106.00	Green	PDF											
20230067	\$100.00	Yellow	PDF											
20240067	\$106.00	Clear	PDF											
20250067	\$106.00	Blue	PDF											

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
95584035	\$8.75	Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h
95584038	\$8.75			230VAC	
95584057	\$8.75			115VAC	



Signal Devices

Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201	\$15.00	PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202	\$14.50	PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503	\$46.00	PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507	\$64.00	PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508	\$84.00	PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522	\$6.00	PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001	\$18.00	PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901	\$21.50	PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902	\$6.00	PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603	\$45.00	PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605	\$10.50	PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]

