



# Signal Devices

## Visual 75mm Base Mount Beacons

### Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- 75mm diameter
- Base mount installation
- Through-hole, cable diameter maximum 10mm
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- Various mounting accessories available
- 2-year warranty



### Visual 75mm Base Mount Beacons 220, 221, and 222 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals							
48mm (Base Mount)																				
<a href="#">22010000</a>	\$33.50	Red	<a href="#">PDF</a>	Incandescent Permanent Light	12–240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-	-4 to 122°F [-20 to 50°C]  IP65 when mounted	up to 5,000h	Polycarbonate cap Polyamide base	97 [3.42]		cULus file E164155, CE, RoHS							
<a href="#">22020000</a>	\$33.50	Green	<a href="#">PDF</a>																	
<a href="#">22030000</a>	\$33.50	Yellow	<a href="#">PDF</a>																	
<a href="#">22040000</a>	\$33.50	Clear	<a href="#">PDF</a>																	
<a href="#">22050000</a>	\$33.50	Blue	<a href="#">PDF</a>																	
<a href="#">22110067</a>	\$100.00	Red	<a href="#">PDF</a>	LED Permanent Light	115VAC	< 25mA	0.5A		up to 100,000h		Max. 2.5 mm² Screwless CAGE CLAMP® - technology (18–14 AWG)									
<a href="#">22120067</a>	Retired	Green	<a href="#">PDF</a>																	
<a href="#">22130067</a>	\$100.00	Yellow	<a href="#">PDF</a>																	
<a href="#">22140067</a>	\$145.00	Clear	<a href="#">PDF</a>																	
<a href="#">22150067</a>	\$145.00	Blue	<a href="#">PDF</a>																	
<a href="#">22110075</a>	Retired	Red	<a href="#">PDF</a>		24V AC/DC	< 45mA														
<a href="#">22120075</a>	\$85.00	Green	<a href="#">PDF</a>																	
<a href="#">22130075</a>	\$85.00	Yellow	<a href="#">PDF</a>																	
<a href="#">22140075</a>	\$127.00	Clear	<a href="#">PDF</a>																	
<a href="#">22150075</a>	\$127.00	Blue	<a href="#">PDF</a>	Xenon Flashing Light (1Hz flash frequency, 1W flash energy)	24VDC	< 100mA	-		4,000,000 flashes		151 [5.33]									
<a href="#">22210055</a>	Retired	Red	<a href="#">PDF</a>																	
<a href="#">22220055</a>	\$127.00	Green	<a href="#">PDF</a>																	
<a href="#">22230055</a>	\$121.00	Yellow	<a href="#">PDF</a>																	
<a href="#">22240055</a>	\$127.00	Clear	<a href="#">PDF</a>																	
<a href="#">22250055</a>	\$127.00	Blue	<a href="#">PDF</a>		115VAC	< 20mA														
<a href="#">22210067</a>	Retired	Red	<a href="#">PDF</a>																	
<a href="#">22220067</a>	\$127.00	Green	<a href="#">PDF</a>																	
<a href="#">22230067</a>	\$121.00	Yellow	<a href="#">PDF</a>																	
<a href="#">22240067</a>	\$127.00	Clear	<a href="#">PDF</a>																	
<a href="#">22250067</a>	\$127.00	Blue	<a href="#">PDF</a>																	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95501535</a>	\$8.75	Bulb for Incandescent Light BA15d Bayonet Socket	7W	24V AC/DC	up to 5,000h
<a href="#">95501537</a>	\$8.75			115VAC	
<a href="#">95501538</a>	\$8.75			230VAC	



# Signal Devices

## Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
<a href="#">97581201</a>	\$15.00	<a href="#">PDF</a>	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.50	<a href="#">PDF</a>	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$46.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$64.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$84.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
<a href="#">97581522</a>	\$6.00	<a href="#">PDF</a>	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
<a href="#">96000001</a>	\$18.00	<a href="#">PDF</a>	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$21.50	<a href="#">PDF</a>	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$6.00	<a href="#">PDF</a>	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$45.00	<a href="#">PDF</a>	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.50	<a href="#">PDF</a>	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]

