



# Signal Devices

## Visual 98mm Tube Mount Beacons

### Features

- Choose from permanent incandescent, permanent LED, flashing Xenon, EVS (Enhanced Visibility System) flashing LED, and rotating models
- Tube mount installation
- 98mm diameter
- Light-intensive Xenon flash in flash models
- Bulb not included with 826 incandescent models
- Various mounting accessories available
- 2-year warranty



### Visual 98mm Tube Mount Beacons 826 and 828 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g[oz]	Connection	Agency Approvals
M25x1.5 (Tube Mount)													
<a href="#">82611000</a>	\$52.00	Red	<a href="#">PDF</a>	Incandescent Permanent Light 98mm	12-240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-	-4 to 122°F [-20 to 50°C]  IP65 when mounted	Up to 5,000h	Polycarbonate cap Polycarbonate/ABS base	231 [8.15]	Terminal screws Max 1.5 mm² Cable diameter 5-7 mm	cULus file E164155, CE, RoHS
<a href="#">82621000</a>	\$52.00	Green	<a href="#">PDF</a>										
<a href="#">82631000</a>	\$52.00	Yellow	<a href="#">PDF</a>										
<a href="#">82641000</a>	\$52.00	Clear	<a href="#">PDF</a>										
<a href="#">82651000</a>	\$52.00	Blue	<a href="#">PDF</a>	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	24VDC	300mA	-	-4 to 122°F [-20 to 50°C]  IP65 when mounted	Min 4,000,000 flashes	Polycarbonate cap Polycarbonate/ABS base	272 [9.59]	Terminal screws Max 2.5 mm² Cable diameter 5-7 mm	
<a href="#">82814055</a>	\$130.00	Red	<a href="#">PDF</a>										
<a href="#">82824055</a>	\$138.00	Green	<a href="#">PDF</a>										
<a href="#">82834055</a>	\$130.00	Yellow	<a href="#">PDF</a>										
<a href="#">82844055</a>	\$138.00	Clear	<a href="#">PDF</a>										
<a href="#">82854055</a>	\$138.00	Blue	<a href="#">PDF</a>		115VAC	65mA 50-60 Hz	-	-4 to 122°F [-20 to 50°C]  IP65 when mounted	Min 4,000,000 flashes	Polycarbonate cap Polycarbonate/ABS base	262 [9.24]	Terminal screws Max 2.5 mm² Cable diameter 5-7 mm	
<a href="#">82814067</a>	\$130.00	Red	<a href="#">PDF</a>										
<a href="#">82824067</a>	\$138.00	Green	<a href="#">PDF</a>										
<a href="#">82834067</a>	\$130.00	Yellow	<a href="#">PDF</a>										
<a href="#">82844067</a>	Retired	Clear	<a href="#">PDF</a>										
<a href="#">82854067</a>	\$138.00	Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



[95582635](#)

Bulbs						
Part Number	Price	Description	Wattage	Voltage	For Use With	Life Duration
<a href="#">95582635</a>	\$8.75	Bulb for incandescent light BA15d bayonet socket	15W	24V AC/DC	826xxxxx	up to 5,000h
<a href="#">95582637</a>	\$8.75			115VAC		
<a href="#">95582638</a>	\$8.75			230VAC		
<a href="#">95588524</a>	\$12.00	Halogen bulb G6.35	20W	12V	885xxx78	Up to 2,000h
<a href="#">95588525</a>	\$12.00			24V	885xxx75	



[95588524](#)



# Signal Devices

## Visual 98mm Tube Mount Beacons

### Visual 98mm Tube Mount Beacons 829 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight [oz]	Connection	Agency Approvals
M25x1.5 (Tube Mount)													
<a href="#">82910755</a>	\$170.00	Red	<a href="#">PDF</a>	Permanent/ Blinking LED (blinking frequency 1.5 Hz)	24VDC	≤ 150mA	≤ 500mA	-4 to 122°F [-20 to 50°C]	up to 50,000h	Polycarbonate cap Polycarbonate/ ABS base	246 [8.68]	Terminal screws ≤ 2.5 mm² Cable diameter 5–7 mm	cULus file E164155, CE, RoHS
<a href="#">82920755</a>	\$224.00	Green	<a href="#">PDF</a>										
<a href="#">82930755</a>	\$170.00	Yellow	<a href="#">PDF</a>										
<a href="#">82950755</a>	\$235.00	Blue	<a href="#">PDF</a>										
<a href="#">82911755</a>	\$199.00	Red	<a href="#">PDF</a>	Rotating LED 98mm	24VDC	≤ 170mA	≤ 500mA	-4 to 122°F [-20 to 50°C]	up to 50,000h	Polycarbonate cap Polycarbonate/ ABS base	259 [9.14]	Terminal screws ≤ 2.5 mm² Cable diameter 5–7 mm	
<a href="#">82921755</a>	\$306.00	Green	<a href="#">PDF</a>										
<a href="#">82931755</a>	\$199.00	Yellow	<a href="#">PDF</a>										
<a href="#">82941755</a>	\$306.00	Clear	<a href="#">PDF</a>										
<a href="#">82951755</a>	Retired	Blue	<a href="#">PDF</a>										
<a href="#">82911768</a>	\$230.00	Red	<a href="#">PDF</a>		115–230 VAC	≤ 200mA	≤ 500mA	IP65 when mounted			275 [9.7]		
<a href="#">82921768</a>	\$335.00	Green	<a href="#">PDF</a>										
<a href="#">82931768</a>	\$230.00	Yellow	<a href="#">PDF</a>										
<a href="#">82941768</a>	\$335.00	Clear	<a href="#">PDF</a>										
<a href="#">82951768</a>	\$335.00	Blue	<a href="#">PDF</a>										
<a href="#">82912755</a>	Retired	Red	<a href="#">PDF</a>	Double Flash LED 98mm	24VDC	≤ 30mA	≤ 500mA	-4 to 122°F [-20 to 50°C]	up to 50,000h	Polycarbonate cap Polycarbonate/ ABS base	257 [9.07]	Terminal screws ≤ 2.5 mm² Cable diameter 5–7 mm	
<a href="#">82932755</a>	\$180.00	Yellow	<a href="#">PDF</a>										
<a href="#">82942755</a>	\$275.00	Clear	<a href="#">PDF</a>					115–230 VAC					
<a href="#">82912768</a>	\$203.00	Red	<a href="#">PDF</a>										
<a href="#">82932768</a>	\$203.00	Yellow	<a href="#">PDF</a>										
<a href="#">82942768</a>	\$283.00	Clear	<a href="#">PDF</a>		Permanent LED 98mm	115VAC	≤ 30mA	≤ 500mA			-4 to 122°F [-20 to 50°C]		
<a href="#">82913767</a>	\$180.00	Red	<a href="#">PDF</a>										
<a href="#">82923767</a>	\$240.00	Green	<a href="#">PDF</a>										
<a href="#">82933767</a>	\$180.00	Yellow	<a href="#">PDF</a>										
<a href="#">82953767</a>	\$257.00	Blue	<a href="#">PDF</a>	Permanent/ blinking / rotating LED 98mm	24VDC	≤ 300mA	≤ 500mA	-4 to 122°F [-20 to 50°C]	up to 50,000h	Polycarbonate cap Polycarbonate/ ABS base	256 [9.03]	Terminal screws ≤ 2.5 mm² AWG 22–14 Cable diameter 5–7 mm	
<a href="#">82915755</a>	\$252.00	Red	<a href="#">PDF</a>										
<a href="#">82925755</a>	\$411.00	Green	<a href="#">PDF</a>										
<a href="#">82935755</a>	\$252.00	Yellow	<a href="#">PDF</a>										
<a href="#">82955755</a>	\$411.00	Blue	<a href="#">PDF</a>	*Enhanced Visibility System (EVS) flashing LED 98mm	24VDC	≤ 300mA	< 500mA	-4 to 122°F [-20 to 50°C]	up to 50,000h	Polycarbonate cap Polycarbonate/ ABS base	256 [9.03]	Terminal screws ≤ 2.5 mm² AWG 22–14 Cable diameter 5–7 mm	
<a href="#">82919755</a>	\$220.00	Red	<a href="#">PDF</a>										
<a href="#">82939755</a>	\$220.00	Yellow	<a href="#">PDF</a>					115–230 VAC					
<a href="#">82949755</a>	\$336.00	Clear	<a href="#">PDF</a>										
<a href="#">82919768</a>	\$254.00	Red	<a href="#">PDF</a>										
<a href="#">82939768</a>	\$254.00	Yellow	<a href="#">PDF</a>										
<a href="#">82949768</a>	\$348.00	Clear	<a href="#">PDF</a>										

\*EVS models provide a random flash pattern for increased visibility.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



# Signal Devices

## Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
<a href="#">97581201</a>	\$15.00	<a href="#">PDF</a>	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.50	<a href="#">PDF</a>	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$46.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$64.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$84.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
<a href="#">97581522</a>	\$6.00	<a href="#">PDF</a>	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
<a href="#">96000001</a>	\$18.00	<a href="#">PDF</a>	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$21.50	<a href="#">PDF</a>	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$6.00	<a href="#">PDF</a>	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$45.00	<a href="#">PDF</a>	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.50	<a href="#">PDF</a>	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]

