





Signal Devices

Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201	\$15.00	PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202	\$14.50	PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503	\$46.00	PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507	\$64.00	PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508	\$84.00	PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522	\$6.00	PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001	\$18.00	PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901	\$21.50	PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902	\$6.00	PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603	\$45.00	PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605	\$10.50	PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]





Signal Devices

Visual 98mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, flashing Xenon, EVS (Enhanced Visibility System) flashing LED, and rotating models
- Base mount installation
- 98mm diameter
- Light-intensive Xenon flash in flash models
- Bulb not included with 826 incandescent models
- 25W bulb included with 827 incandescent models
- Various mounting accessories available
- 2-year warranty



Visual 98mm Base Mount Beacons 826, 827, and 828 Series Selection Chart

Part Number	Price	Color	Drawing link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals		
74mm Base Mount															
82610000	\$41.50	Red	PDF	Incandescent Permanent Light 98mm	12–240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-	-4 to 122°F [-20 to 50°C] IP65 when mounted	Up to 5,000h	Polycarbonate cap Polycarbonate/ABS base	180 [6.35]	Terminal screws Max 2.5 mm² AWG 16–14 Cable diameter 5–8 mm	cULus file E164155, CE, RoHS		
82620000	\$45.00	Green	PDF												
82630000	\$41.50	Yellow	PDF												
82640000	\$45.00	Clear	PDF												
82650000	\$45.00	Blue	PDF												
82710075	\$101.00	Red	PDF	Incandescent Blinking Light (1.5 Hz blinking frequency, 5Ws flash energy) 98mm	24V AC/DC	max. 3.0 A	≤ 3.0 A		4,000,000 flashes	Polycarbonate cap Polycarbonate/ABS base	207 [7.30]				
82720075	\$109.00	Green	PDF												
82730075	\$101.00	Yellow	PDF												
82740075	\$109.00	Clear	PDF												
82750075	\$109.00	Blue	PDF		115V AC/DC	max. 500mA									
82710077	\$101.00	Red	PDF												
82720077	\$109.00	Green	PDF												
82730077	\$101.00	Yellow	PDF												
82740077	\$109.00	Clear	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	24VDC	300mA	≤ 3.0 A	4,000,000 flashes	Polycarbonate cap Polycarbonate/ABS base	220 [7.76]					
82750077	\$109.00	Blue	PDF												
82810055	\$122.00	Red	PDF												
82820055	\$129.00	Green	PDF												
82830055	\$122.00	Yellow	PDF		115VAC	65mA 50–60 Hz									
82840055	\$129.00	Clear	PDF												
82850055	\$207.00	Blue	PDF												
82810067	\$122.00	Red	PDF												
82820067	\$129.00	Green	PDF	115VAC	65mA 50–60 Hz										
82830067	\$122.00	Yellow	PDF												
82840067	\$129.00	Clear	PDF												
82850067	\$207.00	Blue	PDF												

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



[95582635](#)

Bulbs						
Part Number	Price	Description	Wattage	Voltage	For Use With	Life Duration
95582635	\$8.75	Bulb for incandescent light BA15d bayonet socket	15W	24V AC/DC	826xxxxx	up to 5,000h
95582637	\$8.75			115VAC		
95582638	\$8.75			230VAC		
95582735	\$8.50	Bulb for blinking incandescent light B15d bayonet socket	25W	24V AC/DC	827xxxxx	up to 2,000h
95582737	\$8.50			115VAC		
95588524	\$12.00	Halogen bulb G6.35	20W	12V	885xxx78	
95588525	\$12.00			24V	885xxx75	



[95582735](#)



[95588524](#)