



# Audible Signal Devices

## Wall-mount Signal Horns

### Features

- Wall mounting
- Continuous tone
- 148mm diameter

| 570 Series Signal Horns Specifications |                                                   |                             |
|----------------------------------------|---------------------------------------------------|-----------------------------|
| Part Number                            | <a href="#">57005255</a>                          | <a href="#">57005267</a>    |
| Price                                  | \$135.00                                          | \$113.00                    |
| Drawing Link                           | <a href="#">PDF</a>                               | <a href="#">PDF</a>         |
| Description                            | Signal Horn                                       |                             |
| Voltage                                | 24VDC                                             | 115VAC                      |
| Current Consumption                    | 350mA                                             | 200mA                       |
| Tone Frequency                         | 150Hz                                             | 100Hz<br>(supply frequency) |
| Maximum Volume                         | 108dB @ 1m                                        |                             |
| Tone Type                              | Continuous                                        |                             |
| Life Duration                          | > 250h                                            |                             |
| Operating Temperature                  | -20 to 60°C [-4 to 140°F]                         |                             |
| Protection                             | IP55                                              |                             |
| Weight                                 | 880g [31.04 oz]                                   | 860g [30.34 oz]             |
| Housing Material                       | ABS/PC                                            |                             |
| Connection                             | Screwable con max. 2.5 mm² single wire, 18-14 AWG |                             |
| Agency Approvals                       | CE, RoHS                                          |                             |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.





# Audible Signal Devices

## Wall-mount Signal Horns

### Features

- Corrosion-resistant aluminum housing, salt water proof
- Wall mounting
- Continuous tone
- 132mm diameter



| 571 Series Signal Horns Specifications |                                                                  |                             |
|----------------------------------------|------------------------------------------------------------------|-----------------------------|
| Part Number                            | <a href="#">57105255</a>                                         | <a href="#">57105267</a>    |
| Price                                  | \$421.00                                                         | \$384.00                    |
| Drawing Link                           | <a href="#">PDF</a>                                              | <a href="#">PDF</a>         |
| Description                            | Signal Horn                                                      |                             |
| Voltage                                | 24VDC                                                            | 115VAC                      |
| Current Consumption                    | 350mA                                                            | 200mA                       |
| Tone Frequency                         | 150Hz                                                            | 100Hz<br>(supply frequency) |
| Maximum Volume                         | 108dB @ 1m                                                       |                             |
| Tone Type                              | Continuous                                                       |                             |
| Life Duration                          | > 250h                                                           |                             |
| Operating Temperature                  | -20 to 60°C [-4 to 140°F]                                        |                             |
| Protection                             | IP55                                                             |                             |
| Weight                                 | 880g [31.04 oz]                                                  | 860g [30.34 oz]             |
| Housing Material                       | Aluminum                                                         |                             |
| Connection                             | Screwable con<br>max. 2.5 mm <sup>2</sup> single wire, 18-14 AWG |                             |
| Agency Approvals                       | CE, RoHS                                                         |                             |



To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

### Features

- Modern electro-mechanical design
- Wall mounting
- Continuous tone
- 178mm diameter



| 573 Series Signal Horns Specifications |                                                               |                             |
|----------------------------------------|---------------------------------------------------------------|-----------------------------|
| Part Number                            | <a href="#">57300055</a>                                      | <a href="#">57300067</a>    |
| Price                                  | \$183.00                                                      | \$145.00                    |
| Drawing Link                           | <a href="#">PDF</a>                                           | <a href="#">PDF</a>         |
| Description                            | Signal Horn                                                   |                             |
| Voltage                                | 24VDC                                                         | 115VAC                      |
| Current Consumption                    | 350mA                                                         | 200mA                       |
| Tone Frequency                         | 150Hz                                                         | 100Hz<br>(supply frequency) |
| Maximum Volume                         | 105dB @ 1m                                                    |                             |
| Tone Type                              | Continuous                                                    |                             |
| Life Duration                          | > 250h                                                        |                             |
| Operating Temperature                  | -30 to 50°C [-22 to 122°F]                                    |                             |
| Protection                             | IP65                                                          |                             |
| Weight                                 | 1200g [42.33 oz]                                              | 1150g [40.57 oz]            |
| Housing Material                       | Polycarbonate/ABS-blend                                       |                             |
| Connection                             | Screwable con max. 2.5 mm <sup>2</sup> single wire, 18-14 AWG |                             |
| Agency Approvals                       | CE, RoHS                                                      |                             |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.