

# KS 71 Pre-assembled Stacklights



**64924001 and  
64924002**

## KombiSIGN 71 Pre-assembled Stacklights Features

- Available in common voltages of 24 VAC/VDC and 115VAC
- IP65
- LED Permanent Optical Elements
- 70mm diameter/base mount models
- Polycarbonate lens material
- Polyamide glass fiber-reinforced terminal element with cage clamp (part number [64080000](#))

| KS 71 Pre-assembled Stacklights |          |                     |            |                    |           |                  |                              |                |               |
|---------------------------------|----------|---------------------|------------|--------------------|-----------|------------------|------------------------------|----------------|---------------|
| Part Number                     | Price    | Drawing Link        | Voltage    | Colors             | Current   | Starting Current | Operating Temp               | Life Duration  | Weight g [oz] |
| <a href="#">64924001</a>        | \$247.00 | <a href="#">PDF</a> | 115VAC     | Green, yellow, red | max. 20mA | –                | -20 to 50°C<br>[-4 to 122°F] | Up to 100,000h | 249<br>[8.78] |
| <a href="#">64924002</a>        | \$194.00 | <a href="#">PDF</a> | 24 VAC/VDC |                    | max. 25mA | max. 500mA       |                              |                |               |
| <a href="#">64924003</a>        | \$184.00 | <a href="#">PDF</a> | 115VAC     | Green, red         | max. 20mA | –                |                              |                | 191<br>[6.74] |
| <a href="#">64924004</a>        | \$159.00 | <a href="#">PDF</a> | 24 VAC/VDC |                    | max. 25mA | max. 500mA       |                              |                |               |



**64924003 and  
64924004**

| Components for KS 71 Pre-assembled Stacklights |                                                          |                                                      |                                                      |                                               |
|------------------------------------------------|----------------------------------------------------------|------------------------------------------------------|------------------------------------------------------|-----------------------------------------------|
| Image                                          |                                                          |                                                      |                                                      |                                               |
| Part Number                                    | <a href="#">97584001</a>                                 | <a href="#">97584085</a>                             | <a href="#">97584086</a>                             | <a href="#">96000002</a>                      |
| Price                                          | \$20.00                                                  | \$15.00                                              | \$17.00                                              | \$18.00                                       |
| Drawing Link                                   | <a href="#">PDF</a>                                      | <a href="#">PDF</a>                                  | <a href="#">PDF</a>                                  | <a href="#">PDF</a>                           |
| General Description                            | Contact box with side cable exit, with mounting material | Bracket for 1-sided mounting, including rubber seals | Bracket for 2-sided mounting, including rubber seals | Bracket for surface mounting with cable gland |

# Configuring Your KombiSIGN 71 Stack Light

## STEP 1

Select the required optical elements for your application

## STEP 2

Select the optional audible elements for your application



**Optical Signal Elements**

- Incandescent Permanent Light
- LED Permanent Light
- LED Flashing Light
- LED Blinking Light
- LED Rotating Light
- Xenon Flashing Light

**Audible Signal Elements**

- Buzzer Element
- Siren Element

### Plain Base Mount

### Tube Base Mount

## STEP 3

Select the correct terminal element for your mounting option (includes cap)



**Plain Base Mount**

- Screw terminal  
Order no. [64082000](#)
- CAGE CLAMP® terminal  
Order no. [64080000](#)

**Tube Base Mount**

- Screw terminal  
Order no. [64083000](#)
- CAGE CLAMP® terminal  
Order no. [64081000](#)

## STEP 4

Where appropriate, select a base and the desired tube length (only for tube mounting)



**Plain Base Mount**

- Tube with clamp  
Order no. [96000018](#)
- Adapter for single hole mounting  
Order no. [96000025](#)
- Base with integrated tube  
Order no. [97584010](#)

**Tube Base Mount**

- Tube Ø 25 mm, all anodized  
Order no. [97584510](#)  
100 mm long [97584025](#)  
250 mm long [97584040](#)  
400 mm long [97584060](#)  
600 mm long [97584080](#)  
800 mm long [97584090](#)  
1000 mm long [97584003](#)
- Base for Tube, plastic  
Order no. [97584090](#)
- Base for Tube, metal  
Order no. [97584091](#)
- Foldaway Base  
Order no. [96000030](#)
- Tube Ø 25 mm, plastic, only for Foldaway Base, 45 mm long  
Order no. [96000031](#)

## STEP 5

Where appropriate, select the bracket and the contact box.



**Plain Base Mount**

- Contact box with side cable exit  
Order no. [97584001](#)
- Bracket for base mounting  
Order no. [96000002](#)
- Bracket for 1-sided mounting  
Order no. [97584085](#)
- Bracket for 2-sided mounting  
Order no. [97584086](#)

**Tube Base Mount**

- Contact box with side cable exit  
Order no. [97584001](#)
- Contact box with magnetic base and side cable exit  
Order no. [97584004](#)
- Bracket for base mounting with concealed cable entry  
Order no. [96000014](#)
- Bracket for tube mounting  
Order no. [96000001](#)